



Connectors > Socket Connectors > IC & Component Socket Accessories > Heat Sinks



Device Type: SFP

Fin Style: Pin Fin

Number of Fins: 50

Power: 5 W, 10 W, 15 W

Features

Product Type Features

Device Type	SFP
Accessory Type	Clip

Configuration Features

Number of Fins	50
----------------	----

Electrical Characteristics

Power	5 W, 10 W, 15 W
-------	-----------------

Body Features

Fin Style	Pin Fin
Material	Aluminum, Cold-Forged Aluminum
Plating Material	Electroless Nickel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-X29-C1171XN
XFP Cage Assemblies and Kits

TE Part # 1489948-2
XFP HEAT SINK CLIP, PLATED

Customers Also Bought

TE Part #5646442-9
HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm

TE Part #1-2007211-6
MICTOR PLUG ASSY, 76 POS., W/VC

TE Part #1892550-2
MBXL R/A RCPT 2P+24S+2P

TE Part #292497-1
MBXL VERT HDR 2ACP STR

TE Part #3-644284-3
03P MTA156 ASSY 18AWG ORA LF

TE Part #5-6450540-2
MBXL VERT RCPT 1P+16S+1P

TE Part #5535512-5
36 MODII HORZ DR CE

TE Part #5558188-1
MOD JK ASSY, 4P, 8POS, R/A, SHLD



Documents

Product Drawings

HEAT SINK SFP DWDM 10.0mm TALL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1963854-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1963854-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1963854-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English