



Cable Assemblies > Copper Cable Assemblies > Multimedia Cable Assemblies > USB Cable Assemblies



Assembly Type: **USB 4-Position Plug, Type A to Type B**
USB Cable Assembly Configuration: **Double-Ended**
USB Connector Type: **Standard**
Wire Size: **24 – 28 AWG**
USB Cable Assembly Color: **Black**

Features

Product Type Features

Assembly Type	USB 4-Position Plug, Type A to Type B
USB Connector Type	Standard
Shielded	Yes

Configuration Features

Number of USB Connectors	2
USB Cable Assembly Configuration	Double-Ended
Number of Positions	4

Body Features

Ferrite Core	Without
Equalized	Yes
USB Cable Assembly Color	Black

Dimensions


Wire Size	24 – 28 AWG
-----------	-------------

Operation/Application

Halogen Free	No
--------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1903814-1
INDUSTRIAL USB REC ASSY R/A
1ROW

Customers Also Bought




TE Part #1623795-1
Wirewound Resistor: Horizontal Mount



TE Part #1622838-1
CRG0603 1% 12K



TE Part #130677
PG 12-10 RING M10



TE Part #171047-000
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #YDTS24F25-20SNV001
D38999: Jam Nut, 25-20 Insert, Electroless Nickel Plating



TE Part #1-1623773-3
C10 1R0 5% (LOOSE)



TE Part #1622707-1
LR2 1% 1M0



TE Part #1622704-1
LR2 1% 1K5



TE Part #1-2176376-8
RQ 0805 18K7 0.1% 10PPM 1K RL



TE Part #1393556-9
C42334A 302A 13=RP300 MESSERLE

Documents

Product Drawings

CABLE ASSY IND. USB-IND. USB TYPE A

English

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

1-1773463-4_INDUSTRIAL_USB_CONNECTORS

English

Product Specifications

Product Specification

English