



Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Rectangular**
Operating Function: **Off (On)**
Contact Base Material: **Brass**
Switch Contact Plating Material: **Silver**
Dust Proof: **No**

Features

Product Type Features

Illuminated	With
Actuator Style	Rectangular
Dust Proof	No

Configuration Features

Operating Function	Off (On)
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	1

Body Features

Actuator Color	Brown
----------------	-------

Contact Features

Contact Base Material	Brass
Switch Contact Plating Material	Silver
Tactile Switch Contact Current Rating	50 mA

Mechanical Attachment

Tactile Switch Mounting Type	Surface Mount
Tactile Switch Mounting Angle	Vertical

Housing Features



Process Sealed	No
----------------	----

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5-2213819-3 6X6 ILL TACT SMT 520GF LI SOFT ORANGE	 TE Part # 2-2213819-9 6X6 ILL TACT SMT 160GF HI SOFT ORANGE	 TE Part # 4-2213819-5 6X6 ILL TACT SMT 260GF HI SOFT ORANGE	 TE Part # 4-2213819-8 6X6 ILL TACT SMT 260GF HI COLD WHITE
---	---	---	--





TE Part # 2-2213819-3

6X6 ILL TACT SMT 160GF LI RED

Also in the Series | Alcoswitch FSMIJ



Tactile Switches(128)

Customers Also Bought



TE Part #2273120-4

M12 MR-FS DOUBLE END CABLE ASSY BL




TE Part #1-2273110-4

M8 FS - M12 MS CABLE ASSY BL



TE Part #1-2273112-4

M12 MS-FS DOUBLE END CABLE ASSY BL



TE Part #2-2296205-2

22P RCPT VAL-U-LOK GWT/V0



TE Part #2-2213819-5

6X6 ILL TACT SMT 160GF HI BLUE



TE Part #W4S-P012

DEUTSCH DT WEDGELOCKS




TE Part #3-1393292-8

V23074A1002A403-EV-CBOX



TE Part #1-1744057-0

3.96 EP HDR ASSY 10P W/PEGS



TE Part #1218267-3

CONT,CRIMP SKT,20-24AWG,SZ 20



TE Part #2-2213819-4

6X6 ILL TACT SMT 160GF LI COLD WHITE



Documents

Product Drawings

6X6 ILL TACT SMT 160GF HI COLD WHITE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2213819-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2213819-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2213819-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English