
324486 ✔ ACTIVE

TE Internal #: 324486

Splices, Cap, Splice, Copper, Blue, Splice Material Thickness .02 in [. 51 mm], Splice Overall Length .515 in [13.08 mm], Loose Piece, Wire Cap

View on TE.com >

Terminals & Splices > Splices



Splice Product Type: **Cap**

Terminal & Splice Type: **Splice**

Sealable: **No**

Splice Material: **Copper**

Splice Color: **Blue**

Features

Product Type Features

Splice Product Type	Cap
Sealable	No
Serrated	No
Splice Accessory Type	Wire Cap
Splice Barrel Type	Closed Barrel
Splice Wire/Cable Type	Unstripped Wire
Insulated	Yes
Support Style	Non - Insulation Support

Body Features

Plating Material	Tin
Insulation Material	Nylon
Splice Material	Copper
Splice Color	Blue

Contact Features

Terminal & Splice Type	Splice

Mechanical Attachment

Wire Insulation Support	Without

Dimensions

Outside Diameter	5.89 mm[.232 in]
Splice Material Thickness	.51 mm[.02 in]
Splice Overall Length	13.08 mm[.515 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Heavy Duty	No

Industry Standards

Government Qualified Splice	No

Packaging Features

Packaging Quantity	1000
Splice Packaging Method	Loose Piece

Other

Military Category	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 58573-1
SPARE WIRE CAPPER ASSEMBLY



TE Part # 58573-2
PROCRIMP DIE SPARE WIRE CAP

Customers Also Bought



TE Part #1-66359-6
TYPE III CONTACTS STRIP HIGH CURRENT



TE Part #2-34805-1
PIDG RING TONGUE TERMINALS



TE Part #1423162-5
7022AC=RLY,STD,OFF,2P 120VAC,1



TE Part #1423162-7
7022AD=RLY,STD,OFF,2P,120VAC,5



TE Part #225555-6
TNC PLUG DUAL W/P TR



TE Part #2-1423162-9
7022BK=RLY,STD,OFF,M2P,240VAC,



TE Part #167476-000
STD SNAP-ON MARKERS



TE Part #225973-4
PLUG, RT ANGLE, DUAL CRIMP,BNC



TE Part #2151669-1
OCEAN-2.0-APPLICATOR-S-062F120O

TE Part #EC7945-000
HS064WE1NF038B

Documents

Product Drawings

SPARE WIRE CAP,BLU .120-.145 INS.

English

CAD Files

Customer View Model

ENG_CVM_324486_N.3d_igs.zip

English

Customer View Model

ENG_CVM_324486_N.3d_stp.zip

English

Customer View Model

ENG_CVM_324486_N.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

CSA Certificate

English