

OAC-5H

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield OAC

TE Internal #: 2-1393028-9

Potter & Brumfield OAC, Power Relays, Solid State, Contact Arrangement 1 Form A (SPST-NO), Printed Circuit Board Relay Mounting Type

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays > Solid State Relays: PCB mount



Power Relay Type: Solid State

Contact Arrangement: 1 Form A (SPST-NO)

Relay Mounting Type: Printed Circuit Board

[All Solid State Relays: PCB mount \(7\)](#)

Features

Product Type Features

Output Type	AC
Power Relay Type	Solid State

Configuration Features

Output Switching	Zero
------------------	------

Electrical Characteristics

Input Voltage Typical	5 VDC
Output Voltage (Max)	280 V
Output Voltage Rating (AC Relays)	24 – 280 Vrms
Output Current Rating	.05 – 5 Arms
Output Current (Min)	.05 A
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms

Body Features

Product Weight	35 g[1.38 oz]
Case Color	Black



Contact Features

Switch Arrangement	1 Form A (SPST-NO)
Contact Arrangement	1 Form A (SPST-NO)

Termination Features

Relay Termination Type	Printed Circuit Terminals
------------------------	---------------------------

Mechanical Attachment

Coupling	Optical
Relay Mounting Type	Printed Circuit Board

Housing Features

Relay Housing Style	Industry Standard
---------------------	-------------------

Dimensions

Dimensions (L x W x H) (Approximate)	43.1 x 15.2 x 31.7 mm[1.697 x .598 x 1.248 in]
--------------------------------------	--

Usage Conditions

Operating Temperature Range	-30 – 80 °C
-----------------------------	-------------

Operation/Application

R-Switch & slimSSR Relays	No
---------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (88% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-P851-OA1
Solid State Relays: PCB mount

Also in the Series | Potter & Brumfield OAC

Power Relays(7)

Customers Also Bought

TE Part #1-66361-2
TYPE III CONTACTS LP

TE Part #2-1393028-8
Solid State Relays: PCB mountTE Part #1393249-7
W58-XB1A4A-10=W58TE Part #1461477-4
PCN 3A/5A SLIM PCB RELAY 5VDC



TE Part #CB03294012
Single Heavy Wall RW 200 E: Heat Shrink Tubing, 2:1 Shrink Ratio




TE Part #1565917-4
DDR2 SO DIMM Sockets




TE Part #1-5227079-6
COMM BNC PLUG



TE Part #1-2134249-3
D3900 SPRING CLAMP REC 3P w /oSEAL-typeA



TE Part #1217861-1
250 FASTON,PCB TAB,TCBR



TE Part #180908-1
FF 250 TAB HSG 2P NYLON RED

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1393028-9_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1393028-9_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1393028-9_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

OAC AC Output Modules Data Sheet

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide