

328144 ✓ ACTIVE

AMPOWER | AMPOWER

TE Internal #: 328144

AMPOWER, Ring Terminals & Spade Terminals, Rectangular Tongue, 6AWG Wire Size, 13 – 15mm² Wire Size, 20800 – 33100CMA Wire Size, 3/8

[View on TE.com >](#)



Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL 1 STUD HOLE



Terminal & Splice Type: **Rectangular Tongue**

Wire Size: **20800 – 33100 CMA**

Ring & Spade Stud Size: **3/8**

[All AMPOWER TERMINAL 1 STUD HOLE \(51\)](#)

Features

Product Type Features

Ring & Spade Stud Size	3/8
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	Yes
Weight per Piece	6.391 g
Ring & Spade Plating Material	Tin

Contact Features

Military Part Class	Class II
Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment



Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	20800 – 33100 CMA
Stud Diameter	9.91 mm[.39 in]
Tongue Thickness	2.03 mm[.08 in]
Ring & Spade Overall Length	35.81 mm[1.41 in]
Barrel Inside Diameter	5.56 mm[.219 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Box

Other

Comment	Electrodeposited Tin Plate per MIL-T-10727.
---------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMPOWER




Customers Also Bought





TE Part #205606-3
15 POS. SOC. BLOCK



TE Part #EC7548-000
HL104WE1NF033B



TE Part #2-1102660-5
HIP-K.24/64.STS.1.2

Documents

Product Drawings

[TERMINAL,AMPOWER 6 3/8](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_328144_AE.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_328144_AE.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_328144_AE.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPOWER Terminals and Splices Flyer](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[UL Report](#)

English