




Terminals & Splices > Foil Terminals



Foil Terminal Terminal Type: **Barrel**

Body Type: **Type 1**

Foil Thickness (Max): **.76 mm [.03 in]**

Foil Terminal Plating Material: **Tin**

Barrel Wire Size: **12 – 10 AWG**

Features

Product Type Features

Insulated	No
-----------	----

Body Features

Face	Double
Body Type	Type 1
Foil Terminal Plating Material	Tin

Contact Features

Foil Terminal Terminal Type	Barrel
-----------------------------	--------

Termination Features

Foil Thickness (Max)	.76 mm[.03 in]
----------------------	----------------

Dimensions

Barrel Wire Size	3 – 6 mm²
Wire Size	3 – 6 mm²

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	150 °C[302 °F]

Packaging Features

Packaging Quantity	500
--------------------	-----



Foil Terminal Packaging Method

Box

Other

Comment	For heavy duty, use tool 68064.
---------	---------------------------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 49935
DAHT SOLIS 22-10 ASSY



TE Part # 68026
DAHT TERMI-FOIL ASSY



Also in the Series | **TERMI-FOIL**



Foil Terminals(8)



Splices(2)


Customers Also Bought



TE Part #1623729-1
Wirewound Resistor: Vertical Mount



TE Part #2-1879456-1
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #2-1625999-2
Power Resistors: Aluminum Housed, HSC



TE Part #1586000-4
4P FH PLUG VAL-U-LOK V2



TE Part #182524-2
187 FASTON,REC.,17-14 AWG,TPPB



TE Part #2-32952-1
PG R 22-16 COMM 22-18 MIL 10



TE Part #180423-2
110 FASTON,REC.,20-16 AWG,TPBR



TE Part #1624331-1
LT73 3900 2A 1K0 5% 4KRL



TE Part #HD36-18-14PN-072
DEUTSCH HD30 HOUSINGS



TE Part #1974102-1
Copper Shear Bolt Splices up to 35 kV

Documents

Product Drawings

TERMINAL,TERMI-FOIL 12-10

English

CAD Files

Customer View Model

ENG_CVM_330003_E.3d_igs.zip

330003

TERMI-FOIL, Foil Terminals, Barrel, Type 1, Foil Thickness (Max) .03 in [.76 mm], Tin, Barrel Wire Size 12 – 10 AWG, Barrel Wire Size 3 – 6 mm², Box



English

Customer View Model

[ENG_CVM_330003_E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_330003_E.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES](#)

English