



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **7.1 mm [.279 in]**

Recovered Inside Diameter (Max): **3.5 mm [.138 in]**

Shrink Ratio: **2:1**

Features

Product Type Features

Wall Type	Single
-----------	--------

Electrical Characteristics

Voltage (Max)	.3 kV
---------------	-------

Body Features

Fluid Type	None
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Very Flexible

Dimensions

Expanded Inside Diameter (Min)	7.1 mm[.279 in]
Recovered Inside Diameter (Max)	3.5 mm[.138 in]
Heat Shrink Tubing Size Range	3.5 – 7.1 mm[.138 – .279 in]

Usage Conditions

Shrink Temperature (Min)	70 °C
Heat Shrink Tubing Flammability	Highly Flame-Retardant
Operating Temperature Range	-30 – 125 °C
Heat Shrink Tubing Resistance	Strain, Wrinkling



Recovery Temperature	90 °C
----------------------	-------

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Piece
------------------	-------

Other

Meets Low Outgassing Requirements	No
Product Source	US

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | Raychem Versafit V4



Heat Shrink Tubing(27)

Customers Also Bought



TE Part #353908-3
Mini Common Termination (CT) Housings




TE Part #2102353-1
CeeLok FAS-T, Plug Kit, Ni



TE Part #38941-22L
CONTACTS



TE Part #2-179228-3
AMP COMMON TERMINATION HOUSINGS




TE Part #1-103168-2
28 MODII HDR DRST SHRD .100CL




TE Part #1674311-1
TH/.025 CONNECTOR SYSTEM, RECPT AND TAB



TE Part #386997J001
V4-10.0-0-FSP-SM



TE Part #282393-001
81044/13-24-9



TE Part #120553-000
TXR40AB90-0805AI



TE Part #RE11-442S
PLUG ASSY



Documents

Datasheets & Catalog Pages

[VERSAFIT V4 Pages from 9-1773447-9](#)

English

[Application Tooling for Raychem Heat Shrink Product](#)

English

[Very-Thin-Wall, Highly Flame-Retardant, Metric-Sized Heat-Shrinkable Tubing](#)

English

[Measuring_Single_Wall_Tubing](#)

English

[Selecting_Correct_Tubing](#)

English

Product Specifications

[Quality Specification](#)

English