




TE Internal #: 216000-2  
Combo Jacks, Port Matrix Configuration 1 x 1, Single Port, RJ11 / RJ14 / RJ25, Standard Connector Profile, None Status Indicator, Combo Jacks  
[View on TE.com >](#)

Connectors > Modular Jacks & Plugs > Combo Jacks



Port Matrix Configuration: 1 x 1  
Port Configuration: **Single Port**  
Modular Jack & Plug Interface Type: **RJ11 / RJ14 / RJ25**  
Connector Profile: **Standard**  
Status Indicator Type: **None**

Features

Product Type Features

|  |                    |
|--|--------------------|
| Connectors & Connector Components Type | Connector          |
| Modular Jack & Plug Interface Type     | RJ11 / RJ14 / RJ25 |
| Modular Jacks & Plugs Products         | Combo Jacks        |
| Modular Connector Style                | Jack               |
| Grounding Options                      | None               |
| Connector System                       | Cable-to-Panel     |
| Sealable                               | No                 |

Configuration Features

|                            |             |
|----------------------------|-------------|
| Number of Ports            | 1           |
| Port Matrix Configuration  | 1 x 1       |
| Port Configuration         | Single Port |
| Status Indicator Type      | None        |
| Connector Contact Density  | Standard    |
| Number of Positions        | 6           |
| Number of Loaded Positions | 6           |

Body Features

|                                |                       |
|--------------------------------|-----------------------|
| Connector Profile              | Standard              |
| Modular Jack Latch Orientation | Standard - Latch Down |

Contact Features



|                              |                 |
|------------------------------|-----------------|
| Contact Base Material        | Phosphor Bronze |
| Contact Current Rating (Max) | 1.5 A           |

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Connector Mounting Type | Panel Mount |
|-------------------------|-------------|

Housing Features

|                    |                 |
|--------------------|-----------------|
| Housing Color      | Black           |
| Housing Material   | PBT GF          |
| Centerline (Pitch) | 1.02 mm[.04 in] |

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 70 °C[-40 – 158 °F] |
|-----------------------------|---------------------------|

Operation/Application

|                     |        |
|---------------------|--------|
| Shielded            | No     |
| Circuit Application | Signal |

Industry Standards

|                        |           |
|------------------------|-----------|
| UL Flammability Rating | UL 94V-HB |
| Performance Category   | Cat 3     |

Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Quantity | 500 |
| Packaging Method   | Box |

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JUN 2020 (209)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Not applicable for solder process capability  |



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 216003-2  
06P.STUFFER CAP

TE Part # 106307-1  
6P.COVER/SOLD.STOP

Customers Also Bought

TE Part #1658678-1  
D-Sub Crimp: Plug, Signal, 50 Posn,  
Pin Size 22, Shell Size 1

TE Part #205205-7  
D-Sub Crimp Recpt Signal 15 Posn,  
Socket Size 20, Shell Size 2

TE Part #163085-9  
TYPE III CONTACTS STRIP EMEA


TE Part #1766192-1  
CONTACT,PIN,#8

TE Part #1064540-1  
9960 2305 24

TE Part #1879665-6  
H8 14K 0.1% 15PPM

TE Part #1622191-1  
LR0204 1% 20K

TE Part #1658679-1  
D-Sub Crimp: Plug, Signal, 26 Posn,  
Pin Size 22, Shell Size 2



Documents

Product Drawings

6P. TOOLLESS MOD J.

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_216000-2\_F.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_216000-2\_F.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_216000-2\_F.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

application specification for toolless modular jack

English

Application Specification

English