

K400B1F

✓ ACTIVE

Hartman

TE Internal #: 2-1616921-3

DC Contactors, DC Contactor Contact Arrangement SPST NO DB,
400A DC Contactor Contact Current Rating, 28VDC Coil Voltage
(Max)

[View on TE.com >](#)



Relays, Contactors & Switches > Contactors > Mil-Aero Contactors > DC Contactors



DC Contactor Contact Arrangement: **SPST NO DB**

DC Contactor Contact Current Rating: **400 A**

Coil Voltage (Max): **28 VDC**

DC Contactor Coil Resistance: **55 Ω**

DC Contactor Coil Voltage Rating: **28 VDC**

Features

Product Type Features

Arc Cover	Without
Product Classification	Relays - Contactors
Product Type	Contactor
Product Category	Electromechanical Relays
Contactor Type	Sealed
Terminal Configuration	Wire Connector

Electrical Characteristics

Actuating System	DC
Coil Voltage (Max)	28 VDC
DC Contactor Coil Resistance	55 Ω
DC Contactor Coil Voltage Rating	28 VDC
DC Contactor Contact Switching Voltage (Max)	28 VDC

Contact Features

DC Contactor Contact Arrangement	SPST NO DB
DC Contactor Contact Current Rating	400 A
Pole Configuration	1

Termination Features

Coil Termination	Flying Lead
------------------	-------------



Mechanical Attachment

Mounting Plate	Without
DC Contactor Mounting Type	Bus Bar

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 8-1616968-4
K400B1D=CONTACTOR 400 AMP 28
VDC INT



Customers Also Bought




TE Part #205203-3
D-Sub Crimp Recpt Signal 9 Posn,
Socket Size 20, Shell Size 1



TE Part #206966-7
CPC CABLE CLAMPS



TE Part #0641-1-2031L
CONT PIN



TE Part #205089-1
HD 20 PIN CONTACT



TE Part #205090-1
HD 20 SOCKET CONTACT




TE Part #225550-6
TNC PLUG DUAL W/P



TE Part #1-608036-4
SILICONE FUSION TAPE, 1"X15'



TE Part #ZPF000000000007324
983-05 10-05 PN



TE Part #3-103233-9
80 MODII HDR DRST UNSHRD A/PIN



TE Part #316202-000
55A0121-22-0/2

Documents

Product Drawings

K400B1F=CONTACTOR-SPST NO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1616921-3_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1616921-3_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1616921-3_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

K400B1F

DC Contactors, DC Contactor Contact Arrangement SPST NO DB, 400A DC
Contactor Contact Current Rating, 28VDC Coil Voltage (Max)



Datasheets & Catalog Pages

[2-1616921-3_sec6_K400B1F](#)

English