



Terminals & Splices > PCB Terminals



Terminal & Splice Type: **Receptacle**
PCB Terminal Terminal Type: **Receptacle**
PCB Terminal PCB Thickness (Recommended): **1.57 mm [.062 in]**
PCB Terminal Mating Tab Width: **6.35 mm [.25 in]**
PCB Terminal Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Terminates To	Printed Circuit Board
---------------	-----------------------

Configuration Features

Stud Hole	No
Terminal Angle	Straight

Body Features

PCB Terminal Plating Material	Tin
-------------------------------	-----

Contact Features

Terminal & Splice Type	Receptacle
PCB Terminal Terminal Type	Receptacle
Terminal Size	6.35
PCB Terminal Terminal Orientation	Straight

Termination Features

PCB Terminal Termination Method	Through Hole
---------------------------------	--------------

Mechanical Attachment



Wire Insulation Support	Without
-------------------------	---------

Dimensions

PCB Terminal PCB Thickness (Recommended)	1.57 mm[.062 in]
PCB Terminal Mating Tab Width	6.35 mm[.25 in]
PCB Terminal Mating Tab Thickness	.81 mm[.032 in]
Height Above PC Board	13 mm[.518 in]
Extension Below Board	5.5 mm[.216 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

PCB Terminal Packaging Method	Box
-------------------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 725964-2 FASTON 250 PCB TAB .031 TPBR	 TE Part # 140814-2 250 FASTON,TAB,TPBR	 TE Part # 216843-1 250 FASTON,TAB,PCB,TPPB	 TE Part # 141878-2 250 FASTON,TAB,TPBR
 TE Part # 726386-2 FASTON 250 TAB .032 TPBR	 TE Part # 216905-1 POSITIVE LOCK POWER RECEPTACLE TPPHBRZ	 TE Part # 1-726386-2 250 FASTON,TAB,TPBR	 TE Part # 140734-2 250 FASTON,TAB,TPBR
 TE Part # 140596 250 FASTON,TAB,TPBR	 TE Part # 140734-1 250 FASTON,TAB,BR		

Also in the Series | FASTON 250

 Compression Connectors(4)	 Crimp Terminal Housings(143)	 Insertion & Extraction Tools(6)	 Magnet Wire Terminals(1)
-------------------------------	----------------------------------	-------------------------------------	------------------------------



PCB Terminals(144)

Quick Disconnects(466)

Splices(4)

Customers Also Bought

TE Part #1623722-4
Wirewound Resistor: Axial Mount, 17 Watt

TE Part #1-284511-6
16 POS TERMI-BLOK PLUG C. VITI

TE Part #2-1879207-6
RN 0603 360R 0.1% 10PPM CUT LENGTH

TE Part #2-1879207-7
RN 0603 470R 0.1% 10PPM CUT LENGTH

TE Part #1676351-3
RN 0805 48K7 0.1% 10PPM 5KRL

TE Part #2-1393802-1
Signal Relay: Low profile, Monostable DC

TE Part #964187-2
FASTON .110 TAB 0.5 X - NP CUSN4

TE Part #2-1393203-8
V23148-A1007-A101

TE Part #1393640-7
V42254B2101C480=PC612 FEDERLEI

TE Part #1825013-6
MRD10CSTR04=7MM ROT DIP, BCD COMP

Documents

Product Drawings
POSITIVE LOCK 250 TAB PHBRZ
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_216926-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_216926-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_216926-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED](#)

English

[PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

Product Specifications

[Product Specification](#)

English