



Relays, Contactors & Switches > Switches > Slide Switches



Configuration (Pole-Throw): **Four Pole - Double Throw**

Slide Switch Mounting Angle: **Right Angle**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Number of Slide Switch Positions: **4**

Features

Product Type Features

Threaded Case	Without
Grade	Telecom
Switch Type	Slide
Product Type	Switch
Switch Style	Auto-Insertable
Terminal Configuration	Standard
Actuator Style	Flush, Side

Configuration Features

Configuration (Pole-Throw)	Four Pole - Double Throw
Number of Actuators	Single
Number of Slide Switch Positions	4
Operating Function	On On

Electrical Characteristics

Slide Switch Voltage Rating (VDC)	20
-----------------------------------	----

Body Features

Actuator Travel	2.79 mm[.11 in]
Actuator Material	Nylon
Actuator Color	Natural



Contact Features

Contact Base Material	Copper Alloy
Slide Switch Contact Current Rating	.4 A
Switch Contact Plating Material	Gold

Termination Features

Termination Type	PC
------------------	----

Mechanical Attachment

PCB Mount Retention	Without
Slide Switch Mounting Angle	Right Angle
Slide Switch Mounting Type	Through Hole

Dimensions

PCB Tail Length	4.06 mm[.16 in]
Width	7.35 mm[.289 in]
Length	17.78 mm[.7 in]

Identification Marking

Stamped Marking	With
-----------------	------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Other

Comment	Open Ended (Unsealed) Case
---------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed



Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # 2-1825011-2 ASF42G04=4PDT AUTOSLIDE	 TE Part # 1825011-5 ASF22GL04=DPDT AUTOSLIDE	 TE Part # 1825011-1 ASF2204=DPDT AUTOSLIDE	 TE Part # 6-1825011-2 ASF62G04=6PDT AUTOSLIDE
 TE Part # 2-1825011-7 ASF42L04=4PDT AUTOSLIDE	 TE Part # 1825011-2 ASF22G04=DPDT AUTOSLIDE	 TE Part # 1825011-7 ASF22L04=DPDT AUTOSLIDE	 TE Part # 2-1825011-5 ASF42GL04=4PDT AUTOSLIDE
 TE Part # 6-1825011-1 ASF6204=6PDT AUTOSLIDE	 TE Part # 5-1437581-6 ASF22=DPDT AUTO-SLIDE	 TE Part # 1825011-8 ASF22LTR04=DPDT AUTOSLIDE	 TE Part # 2-1825011-1 ASF4204=4PDT AUTOSLIDE



TE Part # 1-1825011-3
ASF22RGL04=DPDT AUTOSLIDE

TE Part # 5-1437581-9
ASF22GL=DPDT AUTOSLIDE L BEND

TE Part # 1-1825011-1
ASF22S04=DPDT AUTOSLIDE

TE Part # 1-1825011-9
ASF22RS04=DPDT AUTOSLIDE

TE Part # 1825011-4
ASF22RG04=DPDT AUTOSLIDE

TE Part # 1825011-6
ASF22GLTR04=DPDT AUTOSLIDE

TE Part # 2-1825011-6
ASF42GLTR04=4PDT AUTOSLIDE

TE Part # 2-1825011-8
ASF42LTR04=4PDT AUTOSLIDE

Also in the Series | Alcoswitch ASE/F

Slide Switches(63)

Customers Also Bought

TE Part #102387-9
40 MODIV HSG COMP DR .100 POL

TE Part #1658622-1
10 NOVO MIL/CTR 30DP,LEAD FREE

TE Part #1757820-2
AMPLIMITE,ASY,RCPT,STD,109,ZN,2

TE Part #1-5532446-9
ASSY,PIN,VERTICAL,HDI,LEAD-FRE

TE Part #1-215083-8
MALE-ON-WIRE CONNECTOR

TE Part #YDTS20F13-35HNV001
D38999: Square Flange, 13-35 insert

TE Part #102541-4
12 AMPMODU MT COVER DR .100CL

TE Part #1-1761692-3
IDC LOW PRO HDR 40P RA LG LAT



Documents

Product Drawings
[ASF42RG04=4PDT AUTOSLIDE](#)
English

CAD Files
[3D PDF](#)
3D
Customer View Model
[ENG_CVM_CVM_2-1825011-4_C.2d_dxf.zip](#)
English
Customer View Model
[ENG_CVM_CVM_2-1825011-4_C.3d_igs.zip](#)
English
Customer View Model
[ENG_CVM_CVM_2-1825011-4_C.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[SWITCHES_CORE_PROGRAM_CATALOG](#)
English