



Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Knob**

Time Delay Relay Input Voltage: **48 VDC**

Time Delay Relay Contact Current Rating: **10A@240VAC A**

Mode of Operation: **On-Delay**

Delay Time: **10 – 100 seconds**

## Features

### Product Type Features

Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays
Magnetic Blow-Out Device	Without

### Configuration Features

Multiple Timing Ranges	Without
------------------------	---------

### Electrical Characteristics

Actuating System	DC
Time Delay Relay Input Voltage	48 VDC

### Contact Features

Contact Arrangement	4 Form C, 4PDT, 4 C/O
Type of Control	Knob
Time Delay Relay Contact Current Rating	10A@240VAC A
Delay Time	10 – 100 seconds

### Termination Features

Termination Type	Screw Terminals
------------------	-----------------

### Mechanical Attachment

--	--

Time Delay Relay Mounting Type

Mounting Bracket

### Dimensions

Dimensions (L x W x H) (Approximate)

114.8 x 65.3 x 71.9 mm[4.523 x 2.572 x 2.832 in]

### Usage Conditions

Operating Temperature Range

-30 – 75 °C

### Operation/Application

Mode of Operation

On-Delay

### Other

Repeatability (Max)

±10%

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)  
Candidate List Declared Against: JAN 2021 (211)  
Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # 1423162-5  
7022AC=RLY,STD,OFF,2P 120VAC,1

## Customers Also Bought



TE Part #1879449-4  
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #2-1618112-2  
WUV-1-120=WILMAR  
UNDERVOLTAGE



TE Part #4-1423159-0  
7012PKL=RLY,STD,ON,2P,125VDC,3




TE Part #7-1393114-9  
KUHP-11D51-48=KU



TE Part #1672124-3  
DP CONTACTORS, 2 POLE




TE Part #1755067-2  
STARX012XSANXA=120VAC/125VDC,  
30MIN



TE Part #1SNK150000R0000  
MC612



TE Part #1SNK706152R0000  
ZK4-PE-4P



TE Part #3-1879695-7  
H8 29K4 0.1% 100PPM



TE Part #4-1393118-8  
KUP-17D19-110=KU

## Documents

### Product Drawings

[7014ND=RLY,STD,ON,4P,48VDC,10](#)

English

### Datasheets & Catalog Pages

[5-1773450-5\\_sec12\\_7000](#)

English

7014ND

Time Delay Relays, Knob, 48VDC Time Delay Relay Input Voltage, 10A@240VACA  
Time Delay Relay Contact Current Rating, On-Delay



[Instruction Sheets](#)

[Instruction Sheet \(U.S.\)](#)

English