



Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Round**
Operating Function: **NO**
Contact Base Material: **Copper Alloy**
Switch Contact Plating Material: **Silver**
Dust Proof: **No**

Features

Product Type Features

Product Type	Switch
Leg Style	Gull Wing
Illuminated	No
Actuator Style	Round
Dust Proof	No

Configuration Features

Tactile Feel	With
ESD Grounding Terminal	Without
Ganged	With
Tactile	Yes
Snap Action	Without
Operating Function	NO
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	1

Electrical Characteristics

Tactile Switch Voltage Rating	24 VDC
-------------------------------	--------

Body Features

Cover Material	Steel
----------------	-------



Case Color	Brown
Actuator Force	160 g[5.648 oz]
Case Material	Polyamide
Bushing Style	Unthreaded
Actuator Profile	Extended
Actuator Material	Polyamide
Actuator Color	Black

Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver
Tactile Switch Contact Current Rating	50 mA

Termination Features

Termination Type	Printed Circuit Board
------------------	-----------------------

Mechanical Attachment

Tactile Switch Mounting Type	Surface Mount
Tactile Switch Mounting Angle	Vertical

Housing Features

Low Profile	With
Process Sealed	No

Dimensions

Actuator Length	1.4 mm[.055 in]
Button Width	3.5 mm[.138 in]
Switch Height	5 mm[.196 in]

Usage Conditions

Temperature Rating	Standard °C
--------------------	-------------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Other

Comment	(On) indicates momentary position.
---------	------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-1437565-7 FSM2JSMA=SMT,TACTILE,PB SWITCH	 TE Part # 1825967-2 FSMCDAH=6.0mm Tact W/SQ Act. & High Temp	 TE Part # 1-1437565-8 FSM1LPATR=TACT SWITCH 6X6MIL S	 TE Part # 2-1437565-8 FSM2JSMAA=TACTILE 260G FORCE S
 TE Part # 1-1437565-9 FSM1LPTR=NEW P/N	 TE Part # 3-1825910-1 FSM16JH=6MM TACT SWITCH, HIGH TEMP	 TE Part # 1-1825955-4 FSM7JH=6MM TACT SWITCH, HT W /ESD	 TE Part # 1-1825027-7 FSMRA6JH04=R/A,TACT PB SW,160G

FSM4JSMATR

Alcoswitch FSMJSMA, Tactile Switches, Round Actuator Style, Operating Function NO, Copper Alloy, Silver, Low Profile




 TE Part # 1437566-4 FSMSMTR=TACT SWITCH	 TE Part # 1-1825910-8 FSM10JH=6MM TACT SWITCH, HIGH TEMP	 TE Part # 1977223-6 FSM2JSMASTR=6MM TACT SWITCH,	 TE Part # 2-1825027-0 FSMRA7JH04=R/A,TACT PB SW,160G
 TE Part # 1825910-6 FSM4JH=6MM TACT SWITCH, HIGH TEMP	 TE Part # 2-1825910-7 FSM14JH=6MM TACT SWITCH, HIGH TEMP	 TE Part # 1825027-8 FSMRA3JH04=R/A,TACT PB SW,160G	 TE Part # 1825027-5 FSMRA2JH04=R/A,TACT PB SW,160G
 TE Part # 1-1825027-4 FSMRA5JH04=R/A,TACT PB SW,160G	 TE Part # 1571300-2 TACT,RTANG,SMT,SEALED,GUID PIN	 TE Part # 1571563-9 FSM8JSMATR=TACT,SMT,T&R	 TE Part # 2-1437565-9 FSM2JSMAATR=TACTILE 260G FORCE

Also in the Series | [Alcoswitch FSMJSMA](#)



Tactile Switches(14)

Customers Also Bought

 TE Part #1473005-1 DDR2 SO DIMM Sockets	 TE Part #1-292253-0 CT 2mm Header Assembly: Right Angle	 TE Part #1734035-2 MINI USB, TYPE B, R/A, SMT	 TE Part #1825910-6 FSM4JH=6MM TACT SWITCH, HIGH TEMP
--	--	--	---

FSM4JSMATR

Alcoswitch FSMJSMA, Tactile Switches, Round Actuator Style, Operating Function NO, Copper Alloy, Silver, Low Profile





TE Part #1825027-5
FSMRA2JH04=R/A,TACT PB SW,160G



TE Part #1625854-3
0603 PROBE PAD




TE Part #1571983-4
GDH04S04=DIP SWITCH



TE Part #1-826634-7
17P MODU 2 PIN HDR



TE Part #1624006-2
SC30-10-2539-10 150UH AMMO 1000



TE Part #9-2176374-7
RQ 0805 1K07 0.1% 10PPM 1K RL

Documents

Product Drawings

FSM4JSMATR=TACT SWITCH 6X6MIL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1437565-2_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1437565-2_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1437565-2_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Products for Mobile Equipment

English

SWITCHES_CORE_PROGRAM_CATALOG

English

Product Environmental Compliance

MD_4-1437565-2_0219201817_dmtec

English



[MD_4-1437565-2_0219201817_dmtec](#)

English