




Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**
Number of Branches/Legs: **5**
Material Code: **100**
Breakout & Transition Material Systems Code: **100**
Adhesive Pre-Coat: **No**

Features

Product Type Features

Molded Part Shape	Y Shape
Size Code	011

Configuration Features

Number of Branches/Legs	5
-------------------------	---

Body Features

Material	Low Fire Hazard Material
Material Code	100
Breakout & Transition Material Systems Code	100
Adhesive Pre-Coat	No

Dimensions

Inside Diameter Range (Leg 2)	3.5 – 6.6 mm[.14 – .26 in]
Inside Diameter Range (Leg 3)	3.5 – 6.6 mm[.14 – .26 in]
Inside Diameter Range (Body)	6.9 – 13.2 mm[.27 – .52 in]
Inside Diameter Range (Leg 1)	3.5 – 6.6 mm[.14 – .26 in]
Inside Diameter Range (Leg 4)	3.5 – 6.6 mm[.14 – .26 in]

Usage Conditions

Flammability	Low Fire Hazard
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]



Operation/Application

Emission Features	Halogen-Free
Power Cable Accessory	No

Industry Standards

Government Qualified	No
----------------------	----

Other

Adhesive Code	S1006, S1030, S1125
Molded Part Shape Code	562A
Fluid/Chemical Resistance	Long-Term Exposure at High Temperature
Breakout & Transition Adhesive Type	Adhesive Purchased Separately

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 095226-000
[S1030-TAPE-3/4X33FT](#)



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Customers Also Bought



TE Part #1658539-3
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



TE Part #180599
SOLIS 8 WIRE PIN




TE Part #1473562-6
[RITS CONN. PLUG ASSY 6P YELLOW](#)




TE Part #1-770252-0
UMNL II PIN LP 14-18



TE Part #1838275-2
[M12 Fld Ser CONN. Male Pin Sld](#)



TE Part #162927-000
[55A1121-16-9/96-9CS2275](#)




TE Part #103946-3
[4X4 MTE SHRD PIN SR POL .100CL](#)



TE Part #YDTS26W17-35SNV001
[D38999: Straight Plug, 17-35 Insert](#)



TE Part #1-770253-0
[UMNLII SOK PTPPHBZ LP LF 24-18](#)



TE Part #1364233001
[5020A3811-0](#)

Documents

Product Drawings

[562A011-100-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-100](#)

English

Raychem Molded Parts Visual Guide

English



Product Specifications

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet