




Energy & Power > Power System Connectors > Wedge Connectors



Wedge Connector Product Availability: **AMERICAS**

Wedge Connector Technology: **Wedge**

Wedge Connector Voltage Class: **≤ 500 kV**

AMPACT Tool Size: **Small**

Features

Product Type Features

|                            |       |
|----------------------------|-------|
| Wedge Connector Technology | Wedge |
|----------------------------|-------|

Configuration Features

|                   |     |
|-------------------|-----|
| Visual Inspection | Yes |
|-------------------|-----|

Electrical Characteristics

|                               |          |
|-------------------------------|----------|
| Wedge Connector Voltage Class | ≤ 500 kV |
|-------------------------------|----------|

Body Features

|                    |        |
|--------------------|--------|
| Conductor Material | Copper |
|--------------------|--------|

Usage Conditions

|  |            |
|--|------------|
|  | 0 – 175 °F |
|--|------------|

Operation/Application

|                                     |          |
|-------------------------------------|----------|
| Application Type                    | Overhead |
| Energized Installation              | Yes      |
| Free of Lead, Cadmium, Heavy Metals | Yes      |

Product Availability

|                                      |          |
|--------------------------------------|----------|
| Wedge Connector Product Availability | AMERICAS |
|--------------------------------------|----------|

Other

|                          |      |
|--------------------------|------|
| Insulated Cover          | No   |
| Cartridge Color Required | Blue |



|                       |       |
|-----------------------|-------|
| Hot Stick Accessories | Yes   |
| AMPACT Tool Size      | Small |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | AMPACT Copper TAP



Customers Also Bought



Documents

Product Drawings

AMPACT CU TAP 350-250

English

Product Specifications

Product Specification

English

Product Specification

English



Tap, AMPACT, Copper

English

Agency Approvals

UL Report

English

UL Report

English