



Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL SLOTTED STUD HOLE



Terminal & Splice Type: Rectangular Tongue

Wire Size: 450000 – 550000 CMA

Ring & Spade Stud Size: 3/8

Stud Diameter: 10.31 mm [.406 in]

[All AMPOWER Terminal Slotted Stud Hole \(4\)](#)

Features

Product Type Features

Ring & Spade Stud Size	3/8
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper

Configuration Features

Number of Holes	2
Terminal Angle	Straight

Body Features

Inspection Slot	No
Weight per Piece	212.281 g
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Offset

Mechanical Attachment

--	--



Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	450000 – 550000 CMA
Stud Diameter	10.31 mm[.406 in]
Tongue Thickness	5.08 mm[.2 in]
Ring & Spade Overall Length	82.55 mm[3.25 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	25
Ring & Spade Packaging Method	Box

Other

Comment	Electrodeposited Tin Plate per MIL-T-10727., Slotted Stud Hole.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46755-2
HYP8 AMPOWER 500MCM DIE SET

Also in the Series | AMPOWER



Bus Bar Connectors(13)



Ring Terminals & Spade Terminals(141)

Customers Also Bought



TE Part #276963-1
AMPOWER TERMINAL SLOTTED STUD HOLE



TE Part #1658674-1
HDP-22,PLUG,SIZE 5,78 POSN



TE Part #3-1437558-5
MTA306D=(MSTA) SW TOG 3PDT



TE Part #2-1393480-8
V23529B1122B209=SUB D FEDERLEI





TE Part #1901776-1
HYP10 15FT HAND CTRL



TE Part #326021
AMPOWER TERMINAL WO HOLE
LONG BARREL



TE Part #2-1437558-0
MTA206N=(MSTA) SW TOG DPDT



TE Part #CV4180-000
RNF-100-1/2-BK-STK-SH



TE Part #2-1618071-3
25-060-7X=WILMAR FREQUENCY 120

Documents

Product Drawings

TERMINAL,AMPOWER 500MCM

English

CAD Files

Customer View Model

ENG_CVM_276964-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_276964-1_C.3d_stp.zip

English

Customer View Model

ENG_CVM_276964-1_C.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPOWER Terminals and Splices Flyer

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)



English

[Agency Approvals](#)

[UL Report](#)

English