




TMS-SCE

TE Internal #: 4575670001  
TMS-SCE, Printable Tubing, Ladder Printable Tubing Type, Military  
Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, White  
[View on TE.com >](#)

Identification & Labeling > Printable Tubing > TMS-SCE MILITARY GRADE SLEEVES



Printable Tubing Type: **Ladder**  
Printable Tubing Grade: **Military**  
Printable Tubing Shrink Ratio: **3:1**  
Primary Product Color: **White**  
Markers per Sleeve: 1

[All TMS-SCE Military Grade Sleeves \(94\)](#)

Features

Product Type Features

|                        |          |
|------------------------|----------|
| Printable Tubing Type  | Ladder   |
| Printable Tubing Grade | Military |

Body Features

|                               |       |
|-------------------------------|-------|
| Printable Tubing Shrink Ratio | 3:1   |
| Primary Product Color         | White |
| Markers per Sleeve            | 1     |

Dimensions

|                                 |                              |
|---------------------------------|------------------------------|
| Product Length                  | 50 mm[2 in]                  |
| Supplied Inner Diameter         | 19 mm[.75 in]                |
| Recovered Inside Diameter       | 6.3 mm[.25 in]               |
| Compatible Cable Diameter Range | 6.9 – 16.2 mm[.275 – .64 in] |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 135 °C[-67 – 275 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                    |                                                              |
|--------------------|--------------------------------------------------------------|
| Recommended Ribbon | See TE Document 411-121005 the Printer Product Ribbon Matrix |
|--------------------|--------------------------------------------------------------|



Printer/Label Features

|                     |                                                              |
|---------------------|--------------------------------------------------------------|
| Recommended Printer | See TE Document 411-121005 the Printer Product Ribbon Matrix |
| Printer Technology  | Thermal Transfer                                             |

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 1000 |
|--------------------|------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1  
T3212-PRINTER

TE Part # 1-2186502-1  
T3224-PRINTER

TE Part # 1-2186503-1  
T3224-SWARE-PRINTER

TE Part # CP8122-000  
T6112DS-PRINTER

TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

Also in the Series | TMS-SCE

Printable Tubing(142)

Customers Also Bought

TE Part #1099510001  
TMS-SCE MILITARY GRADE SLEEVES

TE Part #104479-3  
SHORT POINT CONT 15 DPLX STMPD

TE Part #1052067-1  
2037 5006 02,SMA RA CABLE PLUG

TE Part #2102353-3  
CeeLok FAS-T, Plug Kit, Ni, A

TE Part #187788-000  
SO63-3-00

TE Part #NB10602001  
ATUM-3/1-0-STK



Documents

Product Drawings

TMS-SCE-1K-3/4-2.0-9

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

Instruction Sheets

Instruction Sheet (non U.S.)

English