




Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **Heavy Duty Mini (HDM)**

Features

Other

Applicator & Product Style	Heavy Duty Mini (HDM)
----------------------------	-----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2-2151144-1 OCEAN_2.0_APPLICATOR-S-067F062F	 TE Part # 2151023-1 OCEAN_2.0_Applicator-S-080F120O	 TE Part # 2151858-1 OCEAN-2.0-APPLICATOR-S-122F172F	 TE Part # 2266422-1 OC-AT-S-FM-039F042O-070-1197
 TE Part # 2151144-1 OCEAN_2.0_APPLICATOR-S-067F062F	 TE Part # 2151547-1 OCEAN_2.0_Applicator-S-140F	 TE Part # 2151616-1 OCEAN_2.0_APPLICATOR-S-055F070F	 TE Part # 2151025-1 OCEAN_2.0_APPLICATOR-S-090F200F
 TE Part # 2151011-1 OCEAN_2.0_Applicator-S-042F070F	 TE Part # 2151133-2 OCEAN_2.0_APPLICATOR-S-080F110OV	 TE Part # 2151112-1 OCEAN_2.0_Applicator-S-070F140F	 TE Part # 2151113-1 OCEAN_2.0_APPLICATOR-S-070F102F
 TE Part # 2151743-1 OCEAN_2.0_Applicator-S-080F140OV	 TE Part # 2151030-1 OCEAN_2.0_APPLICATOR-S-062F110F	 TE Part # 2151233-1 OCEAN_2.0_Applicator-S-042F062F	 TE Part # 2151240-1 OCEAN_2.0_APPLICATOR-S-055F075F
 TE Part # 2151092-1 OCEAN_2.0_APPLICATOR-S-080F110OV	 TE Part # 2151174-1 OCEAN_2.0_Applicator-S-090F200F	 TE Part # 2151859-1 OCEAN_2.0_Applicator-S-092F120F	 TE Part # 2151948-1 OCEAN-2.0-APPLICATOR-S-046F057F

Customers Also Bought




TE Part #1633861-1
FLOATING SHEAR



TE Part #1-456403-5
CRIMPER WIRE .062 F




TE Part #1-2119784-8
CRIMPER, INSUL O PREMIUM




TE Part #1-1338690-2
ANVIL, COMBINATION .055



TE Part #1633738-4
CRIMPER, WIRE F



TE Part #1333202-4
ANVIL, COMBINATION (.062)



TE Part #1333231-4
ANVIL, COMBINATION SPECIAL



TE Part #1-2119052-2
PLATE, BASE, SIDE FEED, ATLANTIC
STYLE



TE Part #1320928-2
STRIP GUIDE



TE Part #690482-5
FRONT SHEAR PLATE

Documents

Datasheets & Catalog Pages
CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets
Instruction Sheet (U.S.)

English