

47820 ✓ ACTIVE

AMP

TE Internal #: 47820

Portable Crimp Tools, Premium Crimp Tooling, Removable /Interchangeable, MIL Spec / TE Product Specification (114-), Manual / Battery / Hydraulic

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: MIL Spec, TE Product Specification (114-)

TE Certification: Yes – Certificate Included

Power Technology Type: Battery, Hydraulic, Manual

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content













Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts


 <p>TE Part # 59974-1 HYP8 8-2AWG MANUAL TOOL</p>	 <p>TE Part # 52041 TERMINAL,R PG 8 8</p>	 <p>TE Part # 324082 TERMINAL,T-N R 8 1/4</p>	 <p>TE Part # 53041 TERMINAL,T-N R 8 8</p>
 <p>TE Part # 324045 TERMINAL,T-N R 8 3/8</p>	 <p>TE Part # 52041-1 TERMINAL,R PG 8 1/4</p>	 <p>TE Part # 324043 TERMINAL,T-N R 8 10</p>	 <p>TE Part # 52263-1 TERMINAL R PG 8 10</p>
 <p>TE Part # 52263-5 TERMINAL R PG 8 10</p>	 <p>TE Part # 324044 TERMINAL,T-N R 8 5/16</p>	 <p>TE Part # 328569 SPLC BUTT S.D. S-S T-N 8/12-10</p>	 <p>TE Part # 52291-1 TERMINAL R PG 8 3/8</p>



TE Part # 52291
TERMINAL R PG 8 5/16



TE Part # 52263
TERMINAL R PG 8 10



TE Part # 324625
SPLICE BUTT S-S TERMINYL 8



TE Part # 69051
HYP8 8-2AWG 8T HEAD


Customers Also Bought



TE Part #211825-1
CPC SERIES 4



TE Part #46447
DAHT STRATO 22-10 ASSY



TE Part #159454-000
22759/35-22-9



TE Part #169161-000
55PC1121-20-2/6-9CS2502



TE Part #1-965421-1
TIMER, CONNECTOR HOUSING



TE Part #2063760-1
CCII 187 POSITIVE LOCK REC 24-20
ASSY



TE Part #2560-216-1431
CONT PIN



TE Part #395765-000
55PC0211-18-9CS2502



TE Part #ZPF000000000121739
182-0862-22



TE Part #303848-2
ADJ PIN ASSY

Documents

Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

Bottoming Dies

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)



English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English