



Relays, Contactors & Switches > Contactors > Mil-Aero Contactors > DC Contactors



DC Contactor Contact Arrangement: 1 Form X, SPST-NO-DM

DC Contactor Contact Current Rating: 500 A

Coil Voltage (Max): 12 VDC

DC Contactor Coil Resistance: 11 Ω

DC Contactor Coil Voltage Rating: 12 VDC

Features

Product Type Features

Arc Cover	Without
Product Classification	Relays - Contactors
Product Type	Contactor
Product Category	Electromechanical Relays
Contactor Type	Hermatically Sealed
Terminal Configuration	Flying Lead

Configuration Features

Auxiliary Switch Contact Arrangement	Without
--------------------------------------	---------

Electrical Characteristics

Actuating System	DC
Coil Voltage (Max)	12 VDC
DC Contactor Coil Resistance	11 Ω
DC Contactor Coil Voltage Rating	12 VDC
DC Contactor Contact Switching Voltage (Max)	900 VDC

Contact Features

DC Contactor Contact Arrangement	1 Form X, SPST-NO-DM
DC Contactor Contact Current Rating	500 A



Pole Configuration	1
--------------------	---

Termination Features

Coil Termination	Flying Lead
------------------	-------------

Mechanical Attachment

Mounting Plate	Without
DC Contactor Mounting Type	Side Mount

Dimensions

Coil Wire Length	390 mm[15.3 in]
------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (.35% in plunger) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1618387-5
LEV200A4NAF=RELAY, SPST-NO

Also in the Series | Kilovac LEV200



DC Contactors(15)



Definite Purpose Contactors(1)




General Purpose Contactors(4)



High Voltage Relays(13)

Customers Also Bought



TE Part #1589799-1
JSM015PP2GX006N = WDUALOBE



TE Part #1-1879255-6
RP 2B 57R6 0.1% 15PPM CUT LENGTH




TE Part #YDTS24G23-35SBV001
Jam Nut Receptacle: D38999, Electroless Plating, 23-35 Insert



TE Part #1-1614959-4
CPF0805 2M0 0.1% 25PPM 1K RL



TE Part #1-1532181-1
M83513/03-C15N, MCKS-N1-B-21P6Q1-72.0




TE Part #1059754-1
4584 5018 02




TE Part #1410125-1
MULTIGIG RT T2 1" DC DF F-RGT



TE Part #1410128-1
MULTIGIG RT T2 1" BP FULL RGHT



TE Part #1410132-1
MULTIGIG RT T2 1" DC DF F-STND



TE Part #1589472-2
STG009PC2DX012Q = WDUALOBE



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1618389-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1618389-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1618389-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec7_LEV200

English