



OEG | OEG Power PCB relay OSA

TE Internal #: 5-1419124-9

OEG Power PCB relay OSA, Power Relays, Standard, Monostable, DC, 500 – 600mW Coil Power Rating Class, 540mW Coil Power Rating DC

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Power Relays > STD OEG PCB OMI/OMIH Power Relays



Power Relay Type: **Standard**  
Coil Magnetic System: **Monostable, DC**  
Coil Power Rating Class: **500 – 600 mW**  
Coil Power Rating DC: **540 mW**  
Coil Resistance: **1100 Ω**

[All STD OEG PCB OMI/OMIH Power Relays \(25\)](#)

Features

Product Type Features

Power Relay Type	Standard
------------------	----------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	3500 – 4000 V
Insulation Initial Dielectric Between Open Contacts	1000 Vrms
Contact Limiting Making Current	3 A
Contact Limiting Short-Time Current	3 A
Contact Limiting Continuous Current	3 A
Insulation Creepage Class	5.5 – 8 mm
Insulation Initial Dielectric Between Adjacent Contacts	2500 Vrms
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms
Insulation Initial Resistance	1000 MΩ
Insulation Creepage Between Contact & Coil	7 mm[.276 in]
Contact Limiting Breaking Current	3 A



Coil Magnetic System	Monostable, DC
Coil Power Rating Class	500 – 600 mW
Coil Power Rating DC	540 mW
Coil Resistance	1100 Ω
Coil Special Features	UL Coil Insulation Class A
Coil Voltage Rating	24 VDC
Contact Switching Load (Min)	100mA @ 5V
Contact Switching Voltage (Max)	30 VDC
Contact Voltage Rating	240 VAC

Body Features

Insulation Special Features	7000V Initial Surge Withstand Voltage between Contacts & Coil
Product Weight	13 g[.459 oz]

Contact Features

Contact Arrangement	2 Form A (NO)
Contact Current Class	2 – 5 A, 16 A
Contact Current Rating (Max)	3 A
Contact Material	Ag Alloy
Contact Number of Poles	2
Terminal Type	PCB-THT

Mechanical Attachment

Relay Mounting Type	Printed Circuit Board
---------------------	-----------------------

Dimensions

Length Class (Mechanical)	20 – 25 mm
Insulation Clearance Class	5 – 8 mm
Height Class (Mechanical)	20 – 25 mm
Insulation Clearance Between Contact & Coil	7 mm[.276 in]
Width Class (Mechanical)	12 – 16 mm
Product Width	12.9 mm[.508 in]
Product Length	24.4 mm[.961 in]
Product Height	24.8 mm[.976 in]

Usage Conditions

--	--



Environmental Ambient Temperature Class	50 – 70 °C
Environmental Ambient Temperature (Max)	60 °C[140 °F]

Packaging Features

Packaging Method	Bundle
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-OE4-OS11  
STD OEG PCB OMI/OMIH Power  
Relays



Also in the Series

OEG Power PCB relay OSA

Power Relays(25)

Customers Also Bought

TE Part #1-1879021-7  
SMW3 R47 5%

TE Part #1-1423674-1  
W54-XB1A4A10-30=CKTBKR,THERM,P

TE Part #1-1419130-8  
TSC-109L3H,000

TE Part #1-1879338-2  
CPF 0603 34K8 1% 50PPM 1K RL

TE Part #967650-1  
CIRCULAR DIN HOUSINGS

TE Part #1-1623789-6  
Wirewound Resistor: Vertical Mount

TE Part #1-1721547-1  
PCN 3A/5A SLIM PCB RELAY 3VDC

TE Part #1-1423364-4  
W57-XB1A4A10-10=CKTBKR,THERM,  
PB,QC.250,B

TE Part #1-1969543-4  
ASSY, HDR, VERT, BOSSED, DUAL  
ROW, EP2.5

TE Part #1-1969543-2  
ASSY, HDR, VERT, BOSSED, DUAL  
ROW, EP2.5

Documents

Product Drawings

OSA-SS-224DM3,000

English

CAD Files

3D PDF

3D



Customer View Model

[ENG\\_CVM\\_CVM\\_5-1419124-9\\_F\\_c-5-1419124-9-f.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1419124-9\\_F\\_c-5-1419124-9-f.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-1419124-9\\_F\\_c-5-1419124-9-f.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[OSA Series Relay Data Sheet English](#)

English

Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English

[OSA-SS-224DM3,000 Spec Sheet](#)

Japanese