




Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL 2 STUD HOLES



Terminal & Splice Type: **Rectangular Tongue**

Wire Size: **325000 – 375000 CMA**

Tongue Thickness: **4.32 mm [.17 in]**

Ring & Spade Barrel Type: **Closed Barrel**

Ring & Spade Terminal Orientation: **Straight**

[All AMPOWER TERMINAL 2 STUD HOLES \(26\)](#)

Features

Product Type Features

Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Inspection Slot	Yes
Weight per Piece	93.894 g
Ring & Spade Plating Material	Unplated

Contact Features

Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

--	--



Wire Size	325000 – 375000 CMA
Tongue Thickness	4.32 mm[.17 in]
Ring & Spade Overall Length	73.91 mm[2.91 in]
Barrel Inside Diameter	20.8 mm[.819 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	25
Ring & Spade Packaging Method	Box

Other

Comment	Cleaned but not plated.
---------	-------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 46753-2
HYP8 AMPOWER 350MCM DIE SET




TE Part # 69653
HYP8 AMPOWER 350MCM 69082 DIE SET

Also in the Series | AMPOWER



Bus Bar Connectors(13)



Ring Terminals & Spade Terminals(141)

Customers Also Bought



TE Part #2-6609128-8
CORCOM M SERIES MULTI-FUNCTION INLET FIL




TE Part #325805
AMPOWER TERMINAL 1 STUD HOLE



TE Part #53434-1
AMPOWER KNIFE DISCONNECT



TE Part #1393116-4
KUL-5A15S-120=KU



Documents

Product Drawings

TERM,AMPOWER 350MCM 0 UNPLTD

English

Datasheets & Catalog Pages

AMPOWER Terminals and Splices Flyer

English