



Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL 1 STUD HOLE



Terminal & Splice Type: Rectangular Tongue

Wire Size: 325000 – 375000 CMA

Ring & Spade Stud Size: 1/2, M12

Stud Diameter: 14.27 mm [.562 in]

Tongue Thickness: 4.32 mm [.17 in]

[All AMPOWER Terminal 1 Stud Hole \(51\)](#)

Features

Product Type Features

Ring & Spade Stud Size	1/2, M12
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper

Configuration Features

Number of Holes	2
Terminal Angle	Straight

Body Features

Inspection Slot	No
Weight per Piece	120.96 g
Ring & Spade Plating Material	Tin

Contact Features

Military Part Class	Class II
Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Offset



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	325000 – 375000 CMA
Stud Diameter	14.27 mm[.562 in]
Tongue Thickness	4.32 mm[.17 in]
Ring & Spade Overall Length	101.85 mm[4.01 in]
Barrel Inside Diameter	21.06 mm[.829 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	25
Ring & Spade Packaging Method	Box

Other

Comment	Electrodeposited Tin Plate per MIL-T-10727.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46753-2
HYP8 AMPOWER 350MCM DIE SET



TE Part # 69653
HYP8 AMPOWER 350MCM 69082 DIE SET

Also in the Series | AMPOWER



Bus Bar Connectors(13)




Ring Terminals & Spade Terminals(141)

Customers Also Bought



TE Part #2-323990-1
PIDG RING TONGUE TERMINALS



TE Part #7-1589827-2
SSM005PC2DM012Q = Wdualobe



TE Part #YDTS20F13-98PAV001
D38999: Square Flange, 13-98 insert




TE Part #225107N001
D-1744-04CS378





TE Part #1958540-1
PIDG, R, 22-16/22-18, #6, .260 WDTH



TE Part #1SNA231002R2500
RC510 1->10 (X10) HORIZONTAL



TE Part #2-458141-4
CRIMPER, WIRE



TE Part #479761-000
D-128-0055



TE Part #55842-1
TERMINAL,AMPOWER 600MCM 1/2



TE Part #2-1589457-9
SSM009SC2DC012N = WDUALOBE

Documents

Product Drawings

TERMINAL,AMPOWER 350MCM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_325926-1_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_325926-1_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_325926-1_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPOWER Terminals and Splices Flyer

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)



English

[Agency Approvals](#)

[UL Report](#)

English