

528-AG11D


✕ OBSOLETE

TE Internal #: 5-1437536-5

TE Internal Description: 528-AG11D=SOCKET ASSY

DIP Socket: Standard, Stamped & Formed, Closed, Gold

[View on TE.com >](#)



All DIP Socket: Standard, Stamped & Formed, Closed, Gold (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought

 TE Part #1-1469492-2 MULTIGIG RT 9MM GUIDE/ESD 45 DEG	 TE Part #1-1469492-9 MULTIGIG RT 9MM GUIDE/ESD UNKE	 TE Part #1571626-2 TACT,SMT,GULL WING,50GF,T&R	 TE Part #1-1617028-3 HFW1101K00 = HFW 1/2 SIZE RELA
 TE Part #102617-6 16 MODII HDR DRRR SHRD .100CL	 TE Part #1059350-1 4465 5001 94	 TE Part #102320-1 Universal Headers: Ejector Latch	 TE Part #YDIV40E21-35PBV001 RECP ASSY
 TE Part #1437536-5 DIP Socket: Standard, Screw Machine, Closed, Gold	 TE Part #10206533-00		

Documents

Product Drawings
528-AG11D=SOCKET ASSY

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5-1437536-5_C.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5-1437536-5_C.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5-1437536-5_C.3d_stp.zip
English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[DIP Sockets Quick Reference Guide \(EN\)](#)
English

Product Environmental Compliance
[MD_5-1437536-5_05152014447_dmtec](#)
English
[MD_5-1437536-5_05152014447_dmtec](#)
English