



Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL 1 STUD HOLE



Terminal & Splice Type: Rectangular Tongue

Wire Size: 33100 – 52600 CMA

Ring & Spade Stud Size: 5/16, M8

[All AMPOWER Terminal 1 Stud Hole \(51\)](#)

Features

Product Type Features

Ring & Spade Stud Size	5/16, M8
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	Yes
Weight per Piece	7.294 g
Ring & Spade Plating Material	Tin

Contact Features

Military Part Class	Class II
Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment



Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	33100 – 52600 CMA
Stud Diameter	8.33 mm[.328 in]
Tongue Thickness	2.03 mm[.08 in]
Ring & Spade Overall Length	35.81 mm[1.41 in]
Barrel Inside Diameter	6.99 mm[.275 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	100
Ring & Spade Packaging Method	Box

Other

Comment	Electrodeposited Tin Plate per MIL-T-10727.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1583093-1
DIE ASSEMBLY,AMPOWER,#4

TE Part # 69134-2
HYP8 AMPOWER 4AWG DIE SET

Also in the Series | AMPOWER

Bus Bar Connectors(13)

Ring Terminals & Spade Terminals(141)

Customers Also Bought

TE Part #1-1623728-1
Wirewound Resistor: Vertical Mount

TE Part #1102855-3
AWZG-HVT-RSZ

TE Part #165616-5
110 PIDG FASTON REC

TE Part #130532
PIDG SPADE





TE Part #129501-000
D-SCE FLUID RESISTANT SLEEVES



TE Part #1490599-1
HYP10 TERMINYL 4AWG DIE SET




TE Part #1102855-6
EWZG-RSZ



TE Part #106019-000
CWT-3806



TE Part #1583093-1
DIE ASSEMBLY,AMPOWER,#4



TE Part #926539-6
FASTON 250 HSG PP NAT

Documents

Product Drawings

TERMINAL,AMPOWER 4 5/16

English

CAD Files

Customer View Model

ENG_CVM_328163_S.3d_igs.zip

English

Customer View Model

ENG_CVM_328163_S.3d_stp.zip

English

Customer View Model

ENG_CVM_328163_S.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPOWER Terminals and Splices Flyer

English

Agency Approvals

UL Report

English