



Wire Protection & Management > Heat Shrink Molded Shapes > Wire End Caps



End Cap Wall Type: **Single**
Operating Temperature Range: **-55 – 135 °C**

Features

Product Type Features

End Cap Wall Type	Single
-------------------	--------

Body Features

Color	White
Material	Crosslinked Polyolefin
Shrink Ratio	2:1
Pliancy	Semi-Rigid

Dimensions

Length	19.1 mm[.752 in]
Recovered Inside Diameter (Max)	.8 mm[.031 in]
Cable Diameter Range	1.6 mm
Recovered Wall Thickness (Nominal)	.51 mm[.02 in]
Expanded Inside Diameter (Min)	1.6 mm[.063 in]
Wall Thickness	Thin

Usage Conditions

Fluid Resistance	Aviation Fuel, Chemicals/Solvents, Hydraulic Fluid
Flammability	Flame-Retardant
Heat Shrink Tubing Resistance	Abrasion, Strain, Vibration
Resistance Properties	Splash Protection
Operating Temperature Range	-55 – 135 °C

Operation/Application

--



Emission Free	No
---------------	----

Industry Standards

CSA Certified	No
Government Qualified	No
UL Rating	Recognized

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts















TE Part # 2280355-1
220 V MODEL 17

TE Part # 529535-2
RBK ILS PROCESSOR MK 4

TE Part # 2234800-1
RBK-X1 STD

TE Part # 2234800-2
RBK-X1 CE STD



 <p>TE Part # 2280355-3 110 V MODEL 17</p>	 <p>TE Part # 2280355-4 110 V MODEL 17 REVERSE</p>	 <p>TE Part # 2326489-1 MODEL 105 TUNNEL OVEN, 36" ENTRY, STAND A</p>	 <p>TE Part # 2375310-1 XB17 Belt Heater, 220V</p>
 <p>TE Part # 2375310-2 XB17 Belt Heater, 110V</p>	 <p>TE Part # 2375320-1 XB19 Belt Heater, STD</p>	 <p>TE Part # 2375320-2 XB19 Belt Heater, 150mm (6") Version</p>	 <p>TE Part # 2376800-1 RBK-X1C STD</p>
 <p>TE Part # 2376800-2 RBK-X1C CE STD</p>	 <p>TE Part # 529535-5 RBK-MK 4 EXTERNAL RELEASE + FRONT E-STOP</p>	 <p>TE Part # 529535-6 RBK-MK 4 FRONT E-STOP</p>	 <p>TE Part # 529535-7 RBK-MK 4 INCLUDED AIR COOLING</p>
 <p>TE Part # 529535-8 RBK-MK 4 EXTERNAL RELEASE + AIR COOLING</p>	 <p>TE Part # 955018-000 CLTEQ-M105-TUNNEL-OVEN</p>	 <p>TE Part # 714529-000 CLTEQ-M19-BELT-HTR</p>	 <p>TE Part # 1-528018-1 IR-1891 SHUTTLE RETURN</p>

Also in the Series | Raychem TC Caps



Wire End Caps(3)

Customers Also Bought



TE Part #1662-213-2031
CONT SOC ASSY



TE Part #218204-001
22759/34-20-9



TE Part #2-320093-1
TERMINAL,SOLIS R 16-14 10



TE Part #218203-002
22759/34-22-9




TE Part #160136-001
22759/43-22-9



TE Part #1-225550-2
TNC PLUG




TE Part #YDTS26F15-05PA0000
Straight Plug: D38999, 15-05 Insert, Electroless Nickel Plating



TE Part #109858-000
D-181-1222-90/9



TE Part #1051852-1
2032 5002 00



TE Part #1662-213-1631
CONT SOC ASSY

Documents

Product Drawings

TC-CAPS-4001-9

English

Datasheets & Catalog Pages

TC Caps Pages from 9-1773447-9

English

Application Tooling for Raychem Heat Shrink Product

English

Product Specifications

Quality Specification

English