



Wire Protection & Management > Heat Shrink Molded Shapes > Wire End Caps



End Cap Wall Type: **Single**
Operating Temperature Range: **-55 – 135 °C**

Features

Product Type Features

End Cap Wall Type	Single
-------------------	--------

Body Features

Color	Red
Material	Crosslinked Polyolefin
Shrink Ratio	2.5:1
Pliancy	Semi-Rigid

Dimensions

Length	25.4 mm[1 in]
Recovered Inside Diameter (Max)	1.3 mm[.051 in]
Cable Diameter Range	3.2 mm
Recovered Wall Thickness (Nominal)	.64 mm[.025 in]
Expanded Inside Diameter (Min)	3.2 mm[.126 in]
Wall Thickness	Thin

Usage Conditions

Fluid Resistance	Aviation Fuel, Chemicals/Solvents, Hydraulic Fluid
Flammability	Flame-Retardant
Heat Shrink Tubing Resistance	Abrasion, Strain, Vibration
Resistance Properties	Splash Protection
Operating Temperature Range	-55 – 135 °C

Operation/Application

--



Emission Free	No
---------------	----

Industry Standards

CSA Certified	No
Government Qualified	No
UL Rating	Recognized

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2280355-1
220 V MODEL 17

TE Part # 529535-2
RBK ILS PROCESSOR MK 4

TE Part # 2234800-1
RBK-X1 STD

TE Part # 2234800-2
RBK-X1 CE STD



 TE Part # 2280355-3 110 V MODEL 17	 TE Part # 2280355-4 110 V MODEL 17 REVERSE	 TE Part # 2326489-1 MODEL 105 TUNNEL OVEN, 36" ENTRY, STAND A	 TE Part # 2375310-1 XB17 Belt Heater, 220V
 TE Part # 2375310-2 XB17 Belt Heater, 110V	 TE Part # 2375320-1 XB19 Belt Heater, STD	 TE Part # 2375320-2 XB19 Belt Heater, 150mm (6") Version	 TE Part # 2376800-1 RBK-X1C STD
 TE Part # 2376800-2 RBK-X1C CE STD	 TE Part # 529535-5 RBK-MK 4 EXTERNAL RELEASE + FRONT E-STOP	 TE Part # 529535-6 RBK-MK 4 FRONT E-STOP	 TE Part # 529535-7 RBK-MK 4 INCLUDED AIR COOLING
 TE Part # 529535-8 RBK-MK 4 EXTERNAL RELEASE + AIR COOLING	 TE Part # 955018-000 CLTEQ-M105-TUNNEL-OVEN	 TE Part # 714529-000 CLTEQ-M19-BELT-HTR	 TE Part # 1-528018-1 IR-1891 SHUTTLE RETURN

Also in the Series | Raychem TC Caps



Wire End Caps(3)

Customers Also Bought



TE Part #1662-213-2031
CONT SOC ASSY



TE Part #1-480699-1
02P UMNL CAP HSG BRN




TE Part #ZPF000000000136482
NGC PLUG - FEMALE



TE Part #179544-000
D-181-2222-90/9




TE Part #109858-000
D-181-1222-90/9



TE Part #1SNA168700R2200
PR5



TE Part #1SNA162309R1000
HD6/14.DG



TE Part #1SNA199051R2600
D1.5/6.ADO



TE Part #1SNA199091R1700
D2.5/8.P.ADO



TE Part #1SNA295395R2400
HD10/12.F5.1

Documents

Product Drawings

TC-CAPS-4003-2

English

Datasheets & Catalog Pages

TC Caps Pages from 9-1773447-9

English

Application Tooling for Raychem Heat Shrink Product

English

Product Specifications

Quality Specification

English