



Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL 2 STUD HOLES LONG BAR



Terminal & Splice Type: Rectangular Tongue

Wire Size: 119500 – 150500 CMA

Ring & Spade Stud Size: 1/2, M12

[All AMPOWER Terminal 2 Stud Holes Long Bar \(9\)](#)

Features

Product Type Features

Ring & Spade Stud Size	1/2, M12
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Copper

Configuration Features

Number of Holes	2
Terminal Angle	Straight

Body Features

Inspection Slot	No
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Rectangular Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions



Wire Size	119500 – 150500 CMA
Stud Diameter	14.27 mm[.562 in]
Tongue Thickness	2.79 mm[.11 in]
Ring & Spade Overall Length	113.53 mm[4.47 in]
Barrel Inside Diameter	13.03 mm[.513 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	50
Ring & Spade Packaging Method	Box

Other

Comment	Electrodeposited Tin Plate per MIL-T-10727.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 46767-2
HYP8 AMPPOWER 2/0AWG DIE SET

TE Part # 1583096-1
DIE ASSEMBLY,AMPPOWER,2/0

TE Part # 46323-2
HYP8 AMPPOWER 2/0AWG 69065 DIE SET

Also in the Series | AMPOWER

Bus Bar Connectors(13)

Ring Terminals & Spade Terminals(141)

Customers Also Bought

TE Part #320562
PIDG BUTT SPLICES


TE Part #2-34149-3
PG R 22-16 COMM 22-18 MIL 10

TE Part #T2020002015-000
CDF-1.5


TE Part #3-1105301-1
HVT-C-Bu.Ag.1,5 qmm



TE Part #1-1986469-2
[TSB2000K12DSHT=EUROPA BL,14.5M](#)



TE Part #1-2204910-0
[MBXL R/A HDR 2P + 16S + 2P](#)



TE Part #1658013-5
[MSB0.80PL5ASY200FL,-,10,-TY](#)



TE Part #2-1104012-3
[HVT.35.STI.C](#)



TE Part #3-1105050-1
[HN.D-C-STI.AG.0,75](#)



TE Part #2-1104034-3
[HVT.35.BU.C.SO-SB](#)

Documents

Product Drawings

[TERMINAL,AMPOWER 2/0 1/2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_53681-2_J.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53681-2_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53681-2_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPOWER Terminals and Splices Flyer](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)



English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English