



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #1-647016-2  
Nylon Gold Plated Plug: 2.54mm, With Mating Alignment, MTA 100

TE Part #5-104439-4  
4X5 MTE RCPT SR PLAIN .100CL

TE Part #3-644726-8  
Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100

TE Part #1-87146-4  
40 MODIV HSG COMP DR .150CL



TE Part #3-647476-9  
09P MTA156 PSTD CONN 18AWG LF



TE Part #3-647481-6  
06P MTA156 PSTD CONN 18AWG LF



TE Part #3-647481-9  
09P MTA156 PSTD CONN 18AWG LF



TE Part #306039-000  
44AM1121-18-9/96-9



TE Part #NB13354001  
RNF-100-3/4-CL-SP

Documents

Product Drawings  
AMP 0-57131-2 Rev. M  
English

Datasheets & Catalog Pages  
AMPMODU\_INTERCONNECTION\_SYSTEM\_SECTION3AND4  
English  
IDC Ribbon Cable Brochure  
English

Product Specifications  
Product Specification  
English