



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**
Ratchet Configuration: **Not Releasable, Not Adjustable**
Die Sets Type: **Fixed In Tool**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	Double Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 163304-2 MATENLOK SOCKET SDW	 TE Part # 163305-2 MATENLOK PIN SDW	 TE Part # 163555-6 MATENLOK PIN	 TE Part # 163301-6 MATENLOK PIN
 TE Part # 163301-8 MATENLOK PIN	 TE Part # 163300-8 MATENLOK SOCKET	 TE Part # 163300-6 MATENLOK SOCKET TP	 TE Part # 163558-2 PIN M-N-L
 TE Part # 163304-4 SOCKET MATEN-LOK	 TE Part # 163305-4 PIN MATE-N-LOK	 TE Part # 163555-8 MATE-N-LOK PIN 0,3-	 TE Part # 163558-4 PIN M-N-L



 TE Part # 163300-2 SOCKET MATE-N-LOK	 TE Part # 163304-3 MATENLOK SOCKET	 TE Part # 163555-5 MATE-N-LOK PIN 0,3-	 TE Part # 163555-7 MATE-N-LOK PIN 0,3-
 TE Part # 163558-3 MATE-N-LOK PIN	 TE Part # 163301-1 MATENLOK PIN	 TE Part # 163301-3 MATE-N-LOK PIN	 TE Part # 163301-4 MATE N LOK

Customers Also Bought

 TE Part #163086-2 TYPE III CONTACTS LP EMEA	 TE Part #163558-2 PIN M-N-L	 TE Part #160002 TERM,SOLIS R 2 M10	 TE Part #YDTS24Z21-11ANV001 Jam Nut: D38999, 21-11 Insert, Black Zinc Nickel Plating
 TE Part #154719-6 PL 250 REC HSG 1P NYLON BLUE	 TE Part #163307-2 MATENLOK PIN	 TE Part #163558-4 PIN M-N-L	 TE Part #103682-8 09 MTE PANEL MOUNT SR
 TE Part #163557-2 SOCKET MNL	 TE Part #169400 CERTI-LOK		

Documents



Datasheets & Catalog Pages

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (non U.S.)

English