




Application Tooling > Portable Crimp Tools



TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Tooling Type: **IDC Tooling**

Features

Other

Crimp Form-Wire Barrel Type	Insulation Displacement
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	IDC Tooling
Comment	Used with harness board fixtures

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 <p>TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME</p>	 <p>TE Part # 4-640427-2 12P MTA156 CONN ASSY 20AWG YEL</p>	 <p>TE Part # 4-640427-0 10P MTA156 CONN ASSY 20AWG YEL</p>	 <p>TE Part # 3-640428-8 08P MTA156 CONN ASSY 22AWG RED</p>
 <p>TE Part # 3-640429-7 07P MTA156 CONN ASSY 24AWG WHT</p>	 <p>TE Part # 4-640426-0 10P MTA156 CONN ASSY 18AWG ORA</p>	 <p>TE Part # 3-643817-9 09P MTA156 CONN ASSY 18AWG LF</p>	 <p>TE Part # 4-643818-3 13P MTA156 CONN ASSY 20AWG YEL</p>
 <p>TE Part # 3-640429-6 06P MTA156 CONN ASSY 24AWG WHT</p>	 <p>TE Part # 4-640432-2 12P MTA156 CONN ASSY 20AWG YEL</p>	 <p>TE Part # 3-644460-3 03P MTA156 CONN ASSY 18AWG ORA</p>	 <p>TE Part # 3-640599-7 07P MTA156 CONN ASSY 18AWG ORA</p>
 <p>TE Part # 3-640428-7 07P MTA156 CONN ASSY 22AWG RED</p>	 <p>TE Part # 4-641435-2 12P MTA156 CONN ASSY ORNG</p>	 <p>TE Part # 3-640600-2 02P MTA156 CONN ASSY 20AWG LF</p>	 <p>TE Part # 3-641150-5 05P MTA156 ASSY 22AWG RED LF</p>





TE Part # 3-643818-9
09P MTA156 CONN ASSY 20AWG YEL



TE Part # 3-643817-8
08P MTA156 CONN ASSY 18AWG ORA




TE Part # 4-640427-1
11P MTA156 CONN ASSY 20AWG YEL




TE Part # 4-643819-0
10P MTA156 CONN ASSY 22AWG RED


Customers Also Bought




TE Part #6609036-8
CORCOM SK SERIES SINGLE PHASE FILTERS




TE Part #1879623-8
H4 1K3 0.1% 5PPM




TE Part #103233-7
16 MODII HDR DRST UNSHRD A/PIN




TE Part #3-644896-8
08P CST100 SHRD HDR ASSY LF




TE Part #103321-9
09 MODII HDR SRST B/A .100CL




TE Part #1056450-1
2834 7358 02




TE Part #1380145-2
CLUSTER BLOCK HSG .090 DIA



TE Part #3-103634-3
10 MTE HDR SRRA LATCH .100CL



TE Part #3-103669-0
09 MTE HDR SRST LATCH W/HLDWN



TE Part #3-456401-0
CRIMPER, WIRE .042F

Documents

Datasheets & Catalog Pages
MTA Portable Tooling Solutions

English

Bottoming Dies

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION



English

Instruction Sheets

Mass Termination Assemblies (MTA) 156 Tooling Assembly

English

Instruction Sheet (U.S.)

English