

K10P-11A15-6

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield K10

TE Internal #: 4-1393144-4

Potter & Brumfield K10, Power Relays, Industrial Panel Plug-In, Monostable, AC, 1 – 2VA Coil Power Rating Class, 1.2VA Coil Power Rating AC

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**  
Coil Magnetic System: **Monostable, AC**  
Coil Power Rating Class: **[ 1 – 2 VA ]**  
Coil Power Rating AC: **1.2 VA**  
Coil Resistance: **11 Ω**

Features

Product Type Features

|                  |                          |
|------------------|--------------------------|
| Power Relay Type | Industrial Panel Plug-In |
|------------------|--------------------------|

Electrical Characteristics

|                                                            |                            |
|------------------------------------------------------------|----------------------------|
| Insulation Initial Dielectric Between Coil & Contact Class | 1000 – 1500 V              |
| Insulation Initial Dielectric Between Contacts & Coil      | 1500 Vrms                  |
| Actuating System                                           | AC                         |
| Insulation Initial Dielectric Between Open Contacts        | 1000 Vrms                  |
| Contact Limiting Making Current                            | 10 A                       |
| Contact Limiting Short-Time Current                        | 10 A                       |
| Contact Limiting Continuous Current                        | 10 A                       |
| Insulation Initial Dielectric Between Adjacent Contacts    | 1500 Vrms                  |
| Insulation Initial Resistance                              | 1000 MΩ                    |
| Contact Limiting Breaking Current                          | 10 A                       |
| Coil Magnetic System                                       | Monostable, AC             |
|                                                            | 1 – 2 VA                   |
| Coil Power Rating AC                                       | 1.2 VA                     |
| Coil Resistance                                            | 11 Ω                       |
| Coil Special Features                                      | UL Coil Insulation Class B |
| Coil Voltage Rating                                        | 6 VAC                      |
|                                                            |                            |



|                              |             |
|------------------------------|-------------|
| Contact Switching Load (Min) | 300mA @ 12V |
| Contact Voltage Rating       | 120 VAC     |

Body Features

|                |                |
|----------------|----------------|
| Product Weight | 51 g[1.799 oz] |
|----------------|----------------|

Contact Features

|                              |                       |
|------------------------------|-----------------------|
| Contact Arrangement          | 2 Form C (CO)         |
| Contact Current Class        | 10 – 20 A, 16 A       |
| Contact Current Rating (Max) | 15 A                  |
| Contact Material             | AgCdO                 |
| Contact Number of Poles      | 2                     |
| Terminal Type                | Quick Connect, Solder |

Mechanical Attachment

|                     |        |
|---------------------|--------|
| Relay Mounting Type | Socket |
|---------------------|--------|

Dimensions

|                           |                   |
|---------------------------|-------------------|
| Length Class (Mechanical) | 25 – 30 mm        |
| Height Class (Mechanical) | 30 – 40 mm        |
| Width Class (Mechanical)  | 20 – 25 mm        |
| Product Width             | 21.8 mm[.858 in]  |
| Product Length            | 28.2 mm[1.111 in] |
| Product Height            | 34.9 mm[1.374 in] |

Usage Conditions

|                                         |               |
|-----------------------------------------|---------------|
| Environmental Ambient Temperature Class | 50 – 70 °C    |
| Environmental Ambient Temperature (Max) | 70 °C[158 °F] |
| Operating Temperature Range             | -45 – 70 °C   |

Packaging Features

|                  |      |
|------------------|------|
| Packaging Method | Tray |
|------------------|------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                      |
|-----------------------------------------------|--------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Not Compliant                        |
| EU ELV Directive 2000/53/EC                   | Not Compliant                        |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |




|                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>SVHC > Threshold:<br>Cadmium oxide (5.1% in Component Part)<br><b>Article Safe Usage Statements:</b><br>Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                        | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                                                    |
| Solder Process Capability              | Not applicable for solder process capability                                                                                                                                                                                                                                                                                                                                                                                                           |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                     |                                                                                                                                                      |                                                                                                                                                       |                                                                                                                                      |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 2-1419106-1<br/>27E489=SOCKET,K10,8,QC.187,NYL</p> |  <p>TE Part # 1-1419106-9<br/>27E487=SOCKET,K10,8,SCW,PHEN,G</p> |  <p>TE Part # 2-1419106-7<br/>27E895=SOCKET,K10,8,QC,POLY,NA</p> |  <p>TE Part # 2-1419106-0<br/>27E488=SOCKET</p> |
|-----------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|

Also in the Series | Potter & Brumfield K10

|                                                                                                             |                                                                                                                                       |
|-------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
|  <p>Power Relays(27)</p> |  <p>Relay Accessories, Sockets &amp; Clips(3)</p> |
|-------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|

Customers Also Bought






TE Part #1-487526-7  
2.54mm FFC Connectors Receptacle Housing



TE Part #1-480705-0  
06P UMNL CAP HSG NATL




TE Part #1393143-5  
27E121=SOCKET,KUP,11,SCW,PLE



TE Part #1-5530843-0  
CONN SEC II 43 POS 100C/L



TE Part #1-640721-0  
06P UMNL STR/REL & INSRT NATL



TE Part #1-796638-2  
12POS 5.08MM CE R/A HDR,TRM BK



TE Part #1-770971-0  
10P MINI UMNL R/A HDR ASSY SN



TE Part #1-2232890-3  
3P MONOPLUG 2.5 SELECTIVELY LOADED



TE Part #1-480704-0  
06P UMNL PLUG HSG NATL



TE Part #9-1393253-3  
W69-X2Q12-5=M6/M7/M9/W6/W7

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1393144-4\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1393144-4\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1393144-4\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

K10 15 Amp General Purpose Miniature Relay

English

Industrial Relays Quick Reference Guide



English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

---

**Product Specifications**

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English