



Application Tooling > Portable Crimp Tools



Power Technology Type: **Manual**

Tooling Type: **IDC Tooling**

Features

Other

Crimp Form-Wire Barrel Type	Insulation Displacement
Power Technology Type	Manual
Tooling Type	IDC Tooling

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in



articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # CAT-104MTA-NTPNR Nylon Tin Plated Receptacle: 2.54mm, No Mating Alignment, MTA 100	 TE Part # CAT-104MTA-NTPMR Nylon Tin Plated Receptacle: 2.54mm, With Mating Alignment, MTA 100	 TE Part # CAT-104MTA-NGPNR Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100	 TE Part # CAT-104MTA-NGPMR Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100
 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME	 TE Part # 58075-1 MTA 50/100/156 PNEUMATIC TOOL FRAME	 TE Part # 58338-1 MTA 50/100/156 PNEUMATIC BENCH MOUNT	 TE Part # 3-647080-2 02P MTA100 CONN ASSY ON TAPE
 TE Part # 3-647080-3 03P MTA100 CONN ASSY ON TAPE	 TE Part # 3-647080-5 05P MTA100 CONN ASSY ON TAPE	 TE Part # 647080-2 02P MTA100 CONN ASSY ON TAPE	 TE Part # 647080-3 03P MTA100 CONN ASSY ON TAPE
 TE Part # 931800-1 ELEC PWR UNIT W/O F/TRK OR HD	 TE Part # 3-644314-4 04P MTA100 CONN ASSY 30AU	 TE Part # 3-644314-5 05P MTA100 CONN ASSY 30AU	 TE Part # 3-644314-6 06P MTA100 CONN ASSY 30AU

Customers Also Bought



TE Part #1-917808-3
DYNAMIC 5000 REC AND TAB HSG



TE Part #1747500-2
DYNAMIC 4000 REC AND TAB CONT



TE Part #1-1630027-0
Power Resistors: Aluminum Housed, HSC



TE Part #1630019-4
Power Resistors: Aluminum Housed, HSA



TE Part #2-34110-3
SOLIS R 22-16 COMM 22-18 MIL 6



TE Part #1-1747414-4
DYNAMIC 4000 REC AND TAB HSG



TE Part #1-643075-4
Nylon PCB Connector Covers: 2.54 mm, MTA 100



TE Part #1-1879457-1
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #9-456135-1
CRIMPER, INSULATION "O"(.110")

Documents

Datasheets & Catalog Pages

MTA Portable Tooling Solutions

English

Bottoming Dies

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Terminating Head (Extended-Wear Type) f/MTA-100 Receptacle Connectors

English