



Application Tooling > Portable Crimp Tools



TE Certification: **Cannot be Certified**

Power Technology Type: **Manual, Pneumatic**

Tooling Type: **Head Assembly**

Features

Other

Crimp Form-Wire Barrel Type	Insulation Displacement
TE Certification	Cannot be Certified
Power Technology Type	Manual, Pneumatic
Tooling Type	Head Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability












Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts

 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME	 TE Part # 4-640427-2 12P MTA156 CONN ASSY 20AWG YEL	 TE Part # 4-640427-0 10P MTA156 CONN ASSY 20AWG YEL	 TE Part # 3-640428-8 08P MTA156 CONN ASSY 22AWG RED
 TE Part # 3-640429-7 07P MTA156 CONN ASSY 24AWG WHT	 TE Part # 4-640426-0 10P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-643817-9 09P MTA156 CONN ASSY 18AWG LF	 TE Part # 4-643818-3 13P MTA156 CONN ASSY 20AWG YEL
 TE Part # 3-640429-6 06P MTA156 CONN ASSY 24AWG WHT	 TE Part # 4-640432-2 12P MTA156 CONN ASSY 20AWG YEL	 TE Part # 3-644460-3 03P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-640428-7 07P MTA156 CONN ASSY 22AWG RED
 TE Part # 3-641150-5 05P MTA156 ASSY 22AWG RED LF	 TE Part # 3-643818-9 09P MTA156 CONN ASSY 20AWG YEL	 TE Part # 3-643817-8 08P MTA156 CONN ASSY 18AWG ORA	 TE Part # 4-640427-1 11P MTA156 CONN ASSY 20AWG YEL






TE Part # 4-643819-0
10P MTA156 CONN ASSY 22AWG RED



TE Part # 3-640427-8
08P MTA156 CONN ASSY 20AWG YEL




TE Part # 3-640428-5
05P MTA156 CONN ASSY 22AWG RED




TE Part # 3-643818-5
05P MTA156 CONN ASSY 20AWG YEL


Customers Also Bought




TE Part #1658642-2
D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1




TE Part #1658621-4
20 NOVO MIL/CTR 15DP,LEAD FREE




TE Part #2-32589-1
PIDG SPADE TONGUE TERMINALS




TE Part #1-102976-3
13 MODII HDR SRST B/A .100CL




TE Part #1-699297-1
TIMER, CONNECTOR HOUSING




TE Part #1-1393210-2
PCB Power Relay: 30 Amp, Monostable DC




TE Part #969028-2
TIMER, RECEPTACLE AND TAB



TE Part #2-1633730-4
CRIMPER, WIRE F .062 F



TE Part #180439-2
110 FASTON,REC.,20-16 AWG,TPBR



TE Part #184396-1
2X2 PLUG ASSEMBLY, C KEY, CLAS

Documents

Datasheets & Catalog Pages
MTA Portable Tooling Solutions

English

Bottoming Dies

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION



English

Instruction Sheets

Instruction Sheet (U.S.)

English

Ribbon Cable Terminating Head 58247-3 for MTA-156 Receptacle Connectors

English

Instruction Sheet (U.S.)

English