




Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**  
Ratchet Configuration: **Operator Releasable & Adjustable**  
Die Sets Type: **Removable/Interchangeable**  
Specification Type: **TE Product Specification (114-)**  
TE Certification: **Cannot be Certified**

Features

Other

Crimp Form-Wire Barrel Type	Insulation Displacement
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	IDC Tooling

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed




Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



TE Part # CAT-104MTA-NTPMP  
Nylon Tin Plated Plug: 2.54mm, With Mating Alignment, MTA 100



TE Part # CAT-104MTA-NGPMP  
Nylon Gold Plated Plug: 2.54mm, With Mating Alignment, MTA 100

### Customers Also Bought



TE Part #2-6609107-0  
CORCOM P SERIES MULTI-FUNCTION INLET FIL



TE Part #647000-4  
Nylon Tin Plated Plug: 2.54mm, With Mating Alignment, MTA 100



TE Part #3-641435-4  
04P MTA156 CONN ASSY ORNG



TE Part #2-520264-2  
ULTRAFast 250 ASSY REC 22-18 TPBR LP



TE Part #3-640428-2  
02P MTA156 CONN ASSY 22AWG RED

TE Part #3-641435-2  
02P MTA156 CONN ASSY ORNG

TE Part #104505-6  
MTE PIN 22-26 AWG PLTD

TE Part #2-1633730-4  
CRIMPER, WIRE F .062 F

TE Part #2-2119582-3  
Crimper, Insulation F Premium

TE Part #2-1658527-0  
622-1230LF=FSKT IDC S 12 30AU

Documents

Datasheets & Catalog Pages

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Terminating Head 58638-1 f/MTA-100 Posted Connectors

English

Instruction Sheet (U.S.)

English