



Energy & Power > Power System Connectors > Wedge Connectors > AMPACT Wedge Pressure Tap Connectors



Wedge Connector Product Availability: AMERICAS, ANZPAC, ASIA, China, EMEA

Wedge Connector Technology: Wedge

Wedge Connector Voltage Class: 0 – 500 kV

AMPACT Tool Size: Large

[All AMPACT Wedge Pressure Tap Connectors \(61\)](#)

Features

Product Type Features

Wedge Connector Technology	Wedge
----------------------------	-------

Configuration Features

Visual Inspection	Yes
-------------------	-----

Electrical Characteristics

Wedge Connector Voltage Class	0 – 500 kV
-------------------------------	------------

Usage Conditions

	-40 – 150 °F
--	--------------

Operation/Application

Application Type	Overhead Transmission & Distribution Connections
Energized Installation	Yes
Free of Lead, Cadmium, Heavy Metals	Yes

Industry Standards

RUS Approved	Yes
--------------	-----

Product Availability

Wedge Connector Product Availability	AMERICAS, ANZPAC, ASIA, China, EMEA
--------------------------------------	-------------------------------------

Other



Insulated Cover	Yes
High Temperature is Available	200 °F
Cartridge Color Required	Yellow
Hot Stick Accessories	Yes
AMPACT Tool Size	Large

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series

AMPACT ALUMINUM TAP



Customers Also Bought



Documents

Product Drawings

CONNECTOR, 795.0 SERIES,AMPACT

English

Datasheets & Catalog Pages

AMPACT ALUMINUM TAP CONNECTORS

English



Instruction Sheets

Customer Manual (U.S.)

English

Customer Manual (U.S.)

English

Agency Approvals

UL Report

English