

524-AG11D-ESL


✕ OBSOLETE

TE Internal #: 4-1437536-2

TE Internal Description: 524-AG11D-ESL=SOCKET ASSY

DIP Socket: Standard, Stamped & Formed, Closed, Gold

[View on TE.com >](#)



All DIP Socket: Standard, Stamped & Formed, Closed, Gold (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



 TE Part #1676366-2 RN 0805 51R1 0.1% 10PPM 1KRL	 TE Part #D561523001 RAY-101-4.0(100)	 TE Part #130191 TERM, SOLIS R 12-10 5MM	 TE Part #1-1478031-0 BNC Ins LP PCB Skt 75Ohm White
 TE Part #1676230-2 RN 0805 1K37 0.1% 10PPM 1KRL	 TE Part #1-644487-4 Polyester Vertical PCB Header: 2.54 mm, Shrouded, MTA 100	 TE Part #102321-7 AMP-LATCH UNIVERSAL HEADERS	 TE Part #1625895-5 25MM DIA E/WHEEL [BLACK]
 TE Part #1-794130-1 09P MINI UMNL HDR ASSY BLMT LF	 TE Part #1-1768812-3 LBC-11017		

Documents

Product Drawings

524-AG11D-ESL=SOCKET ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1437536-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1437536-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1437536-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



DIP Sockets Quick Reference Guide (EN)

English