



Identification & Labeling > Labels > Standard Labels > LE WHITE LABELS



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent Pressure Sensitive Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **38.1 mm [1.5 in]**

[All LE WHITE LABELS \(12\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	5
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	38.1 mm[1.5 in]
Label Height	19.1 mm[.75 in]
Label Material	Polyester
Label Thickness	80 Micron

Industry Standards

UL Listed	Yes
-----------	-----

Packaging Features



Packaging Method	Sheet
Other	
Label Adhesive Type	Permanent Pressure Sensitive Acrylic Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186545-1
WINTOTAL-7-DONGLE



TE Part # 1-2186546-1
WINTOTAL-7-END-USER-LICENCE

Customers Also Bought



TE Part #8-2176388-2
RQ 1206 69R8 0.1% 10PPM 5K RL

TE Part #1744037-8
08P EC PWR.200 CL HDR ASSY VRT

TE Part #5-534998-3
06 MODIV VRT DR CE 100/125

TE Part #104506-8
MTE PIN 28-32 AWG PLTD

TE Part #50864-5
Mini Spring Sockets: Open Bottom, 5A

TE Part #598230-000
LM METALIZED POLYESTER LABELS

TE Part #66084-2
CONT AMP LEAF L/P 100 SN

TE Part #104503-8
09 MTE PIN HSG SR RIB .100CL

TE Part #1623857-9
409HS 5K 008 KNOB

TE Part #CTJ420E017
ELEC MODULE

Documents

Product Drawings

308-LE

English

Datasheets & Catalog Pages

LE White Polyester labels

English

IDENTIFICATION SELECTION GUIDE

English