




DIPLOMATE 800 Series

TE Internal #: 4-1571552-2

TE Internal Description: 814-AG11D-ES-LF=800 DIP,AU/SN

DIP Socket: Standard, Stamped & Formed, Open, Gold

[View on TE.com >](#)



All DIP Socket: Standard, Stamped & Formed, Open, Gold (4)

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | DIPLOMATE 800 Series



DIP Sockets(5)

Customers Also Bought

TE Part #1-213825-7
CPC SERIES 1 POSTEDTE Part #2-1571552-2
DIP Socket: Standard, Stamped & Formed, Open, GoldTE Part #2-1437597-3
2SWK132AL101=NON UL KEYLOCKS STE Part #2-1879061-7
CPF 0402 100R 0.1% 25PPM 5K RLTE Part #9-2176307-9
RP 1E 0.1W 130K 0.1% 25PPM 5K RLTE Part #1622516-1
LR1 1% 560KTE Part #1969795-1
02P UMNL HDR ASSY SCKT V0 GWTE Part #1622314-2
LR1 1% 133KTE Part #1437539-6
808-AG11D-ESL=SOCKET ASSY

Documents

Product Drawings

814-AG11D-ES-LF=800 DIP,AU/SN

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_4-1571552-2_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1571552-2_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1571552-2_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DIP Sockets Quick Reference Guide \(EN\)](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English