



## AMP

TE Internal #: 6-1579014-2

Portable Crimp Tools, Commercial Crimp Tooling, Operator  
Releasable & Adjustable, Removable/Interchangeable, TE Product  
Specification (114-)

[View on TE.com >](#)

Application Tooling &gt; Portable Crimp Tools

Tool Grade: **Commercial Crimp Tooling**Ratchet Configuration: **Operator Releasable & Adjustable**Die Sets Type: **Removable/Interchangeable**Specification Type: **TE Product Specification (114-)**TE Certification: **Cannot be Certified**

## Features

### Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Electric, Manual
Tooling Type	Ergocrimp Hand Tool Assembly or Die

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per

homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 8-1579022-5  
ERGOCRIMP DIE MCON 1,5-2,5 SWS

### Customers Also Bought



TE Part #58593-1  
PROCRIMP PQ



TE Part #1823373-1  
TIMER, CONNECTOR HOUSING



TE Part #2-1633930-6  
ANVIL, COMBINATION



TE Part #2150334-2  
OCEAN\_2.0\_Applicator-S-090F130F



TE Part #2151604-2  
OCEAN-2.0-APPLICATOR-S-100F155OV



TE Part #2151928-2  
OCEAN\_2.0\_Applicator-S-055F135O



TE Part #2358638-1  
DIE SET DIA 6MM T 6MM2



TE Part #2358774-1  
DIE SET DIA 6MM T 25MM2



## Documents

### Product Drawings

[ERGOCRIMP HAND TOOL MCON 1,5-2,5 SWS](#)

German

### Datasheets & Catalog Pages

[1-1773865-2\\_1015\\_Commercial Manual Hand Tools](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

### Bottoming Dies

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English