



Relays, Contactors & Switches > Contactors > Mil-Aero Contactors > DC Contactors



DC Contactor Contact Arrangement: 1 Form X, SPST-NO DM

Wire Size: .34 mm²

DC Contactor Contact Current Rating: 100 A

Coil Voltage (Max): 24 VDC

Features

Product Type Features

Product Classification	Relays - Contactors
Product Type	Contactor
Product Category	Electromechanical Relays
Contactor Type	Sealed
Terminal Configuration	2 x M4 Bolt

Configuration Features

Auxiliary Switch Contact Arrangement	None
--------------------------------------	------

Electrical Characteristics

Actuating System	DC
Coil Voltage (Max)	24 VDC
DC Contactor Coil Resistance	96 Ω
DC Contactor Coil Voltage Rating	24 VDC
DC Contactor Contact Switching Voltage (Max)	900 VDC

Contact Features

DC Contactor Contact Arrangement	1 Form X, SPST-NO DM
DC Contactor Contact Current Rating	100 A
Pole Configuration	1

Termination Features

Coil Termination	Wire
------------------	------



Mechanical Attachment

DC Contactor Mounting Type	Side Mount
----------------------------	------------

Dimensions

Coil Wire Length	381 mm[15 in]
Wire Size	.34 mm²

Packaging Features

Packaging Method	Individual
------------------	------------

Other

Torque	30 – 40 in-lbs
--------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1618387-5
LEV200A4NAF=RELAY, SPST-NO



TE Part # 9-1618389-8
LEV100A5ANG=RELAY, SPST, 24Vdc

Also in the Series | Kilovac LEV100



DC Contactors(11)



High Voltage Relays(3)

Customers Also Bought



TE Part #120955-1
TE UPM R/A Header 5P HC Power, LLLLL



TE Part #1-212565-0
AMPLIMITE,PIN CONT,SZ 20,AU PLTD



TE Part #1-1623894-2
416P 5K




TE Part #1-1757824-1
AMPLIMITE,ASY,RCPT,STD,90,ZN,5,CT



TE Part #1-2176330-5
CRGP 2010 150R 1%




TE Part #YDTS26F25-35SNV001
D38999: Straight Plug, 25-35 Insert




TE Part #1-215309-6
2X16P HV100 REC CON. TE, 8.5MM



TE Part #1218125-5
50 POS,ASSY,PLUG,LOW PROF,109



TE Part #1-2000713-0
RA Keyed Guide Mod, Vita 46, Machined



TE Part #1062-20-0222-PS
SOC SZ20 PS 16-22AWG .051-.085 INS NKL



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1618391-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1618391-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1618391-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Kilovac LEV100 Series 900 Vdc Contactor

English