



Application Tooling > Spare & Wear Tooling



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 466625-4
APPL,HDM 5SAPR042F055O G



TE Part # 466819-2
APPL,HDM 5SMPR042F055O K



TE Part # 466918-1
APPL,SCA 9SMPR042F062O S



TE Part # 466983-1
SCAMSP0042F055O

Customers Also Bought



TE Part #1-640251-0
3.96mm Wire-to-board housing:
receptacle, no mating alignment, SL
156



TE Part #2-324159-2
PIDG RING TONGUE TERMINALS



TE Part #102387-9
40 MODIV HSG COMP DR .100 POL



TE Part #1969116-1
187 & 250 FASTON HSG.,REC.,3 POS,
NATURAL



TE Part #1658690-1
D-Sub Crimp Recpt Signal 15 Posn,
Socket Size 22, Shell Size 1




TE Part #F51654-000
WV HIGH TACK WHITE VINYL LABELS



TE Part #2-1633730-7
CRIMPER, WIRE F .042F



TE Part #1241980-8
SPECIAL STANDARD TIMER
HOUSING 8POS



TE Part #1855118-1
U POD .187 STRAIGHT SAPR090F140F
LM & G



TE Part #1-455888-2
SPACER, CRIMPER((060)

Documents

Datasheets & Catalog Pages
CRIMPING WHERE FORM MEETS FUNCTION
English

Instruction Sheets
Instruction Sheet (U.S.)
English