

47824 ✓ ACTIVE

AMP

TE Internal #: 47824

Portable Crimp Tools, Premium Crimp Tooling, Removable /Interchangeable, TE Product Specification (114-) / MIL Spec, Manual / Hydraulic / Battery

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: MIL Spec, TE Product Specification (114-)

TE Certification: Yes – Certificate Included

Power Technology Type: Battery, Hydraulic, Manual

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 324057
 TERMINAL,T-N R 1/0 3/8



TE Part # 324058
 TERMINAL,T-N R 1/0 1/2



TE Part # 324056
 TERMINAL,T-N R 1/0 1/4



TE Part # 55822-1
 TERMINAL T-N R 1/0 1/4



TE Part # 58422-1
 HYP8 8-4/0AWG 33T HEAD



TE Part # 324113
 TERMINAL,T-N R 1/0 5/16



TE Part # 69066
 HYP8 8-4/0AWG 22T HEAD



TE Part # 1752787-1
 HYP10 8-4/0AWG 33T HEAD



TE Part # 1752877-1
 HYP10 8-4/0AWG 22T HEAD

Customers Also Bought



TE Part #1658610-2
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm



TE Part #1-794611-1
MICRO MNL RPT CNT,LS PC,15AU,L



TE Part #1-331421-1
TERMINAL,T-N R 4HD 3/8



TE Part #1624281-1
SP1 220R 5% TAPED



TE Part #1-331421-0
TERMINAL,T-N R 4HD 5/16




TE Part #1-1604800-4
ASSY,PLUG,QUADRAX,FREE HANGING,12 POS



TE Part #1-966658-1
32pos MQS .63 header 180deg



TE Part #076147-000
CTC-0062-18-9/5-9



TE Part #114721-000
55PC0711-14-9CS2502



TE Part #ZPF0000000000037216
983-6SE 24-30 S6 L

Documents

Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

Bottoming Dies

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English