



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

Applicator & Product Style	OCEAN
----------------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>








Compatible Parts

 TE Part # 1-687395-8 HINGE BAR 9EAPR160T180O G	 TE Part # 1852633-1 EAPOHB160TABLOCK180O LM/G-HINGE BAR	 TE Part # 1852895-1 HDM EMPO K-HINGE BAR	 TE Part # 1855041-1 HINDGE BAR F.A. EMPO160TAB180O LM & G
 TE Part # 1855465-1 HDM w/FA HINGE BAR EAPR160TAB-LOCK180O	 TE Part # 1855468-1 HDM/FA/HB EMPO160TABLOCK180O LM & G	 TE Part # 1855601-1 HDM/FA EAPRHB.160TABLOC.180O G CUT	 TE Part # 567303-1 APPL,HINGE BAR 9EMPO160T180O T
 TE Part # 567408-2 HDMHB 9EAPR160T180O G	 TE Part # 680194-3 HDM*HB* 9EAPR160T180O G	 TE Part # 687395-8 HINGE BAR 9EAPR160T180O G	 TE Part # 687395-9 EF HINGE BAR 9EMPR160TL210O T
 TE Part # 7-1855041-7 SPARE PART KIT	 TE Part # 1852633-2 EAPRHB160TABLOCK180O K - HINGE BAR	 TE Part # 297530-2 MINI APLICADOR END FEED	 TE Part # 687395-1 END FEED HINGE BAR APPLICATOR

Customers Also Bought



 TE Part #1376395-1 Power Key TPA	 TE Part #179463-2 DBL LOCK CAP F/H 2P RED	 TE Part #179974-1 250 PL EX REC. 18-14AWG PTBR	 TE Part #1747063-1 Sig GRACE INERTIA Receptacle
 TE Part #1376392-2 STD Temp Power Key Plug	 TE Part #179970-2 PL EXII 250 REC HSG 1P NYLON RED	 TE Part #1318954-6 250 HSG. PL EX REC. BLUE	 TE Part #174817-2 250 sleeve PL YELLOW transparent
 TE Part #1-178708-1 187 SLEEV PL EX FLAG NAT	 TE Part #937157-1 WIRE CRIMPER		

Documents

Datasheets & Catalog Pages

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English