



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability


Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 35665 TERMINAL,SOLIS R 8 5/8	 TE Part # 35664 TERMINAL,SOLIS R 8 1/2	 TE Part # 33463 TERMINAL,SOLIS R 8 3/8	 TE Part # 130550 SOLIS 8 R M6
 TE Part # 31808 TERMINAL,SOLIS R 8 5/16	 TE Part # 33462 TERMINAL,SOLIS R 8 5/16	 TE Part # 160013 SOLIS 8 R M5	 TE Part # 160056 SOLIS 8 R 10MM
 TE Part # 36906 SPLICE,SOLIS BUTT 8	 TE Part # 32996 TERMINAL,SOLIS R 8 8	 TE Part # 34321 SPLICE,SOLIS BUTT 8	 TE Part # 323168 TERMINAL,SOLIS R HR 8 3/8

 TE Part # 184064-1 TERMINAL,SOLIS R 8 10MM	 TE Part # 180599 SOLIS 8 WIRE PIN	 TE Part # 2-324061-5 TERMINAL,SOLIS R 8 8 HR	 TE Part # 33460 TERMINAL,SOLIS R 8 10
 TE Part # 35247 TERMINAL,SOLIS R 8 1/4	 TE Part # 324061 TERMINAL,SOLIS R 8 8	 TE Part # 322445 TAB,SOLIS 8	 TE Part # 34318 SPLICE,SOLIS PARA 8

Customers Also Bought

 TE Part #329389 PIDG RING TONGUE TERMINALS	 TE Part #323868 TERMINAL,SOLIS R 3/0 1/4	 TE Part #2-33722-1 TERMINAL,DG R 16-14HD 10	 TE Part #3-1658527-2 622-6441LF=FSKT IDC S 64 30AU
 TE Part #2-31771-1 TERMINAL,DG R 12-10 10	 TE Part #2150258-1 OCEAN_2.0_Applicator-E-090F140F	 TE Part #2266483-1 OC-AT-S-FM-067F077O-023-0442	 TE Part #2836244-1 OCEAN-2.0-APPLICATOR-S-090F155O
 TE Part #NB17272001 RP-4800-NO.10-0-STK	 TE Part #2-456134-1 CRIMPER, INSULATION "F"(.090")		

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Product Specifications

Safety Precautions

English

Safety Precautions

French

Instruction Sheets

Instruction Sheet (U.S.)

English