

RNF-100-1/4-4-SP ✓ ACTIVE

Raychem | Raychem RNF-100

TE Internal #: 5053114035

Raychem RNF-100, Heat Shrink Tubing, Yellow, Single Wall Type, 6.4 Expanded Inside Diameter (Min) .25 Expanded Inside Diameter (Min)

[View on TE.com >](#)



Heat Shrink Tubing > RNF-3000 Single Wall Stick Heat Shrink



Primary Product Color: **Yellow**

Wall Type: **Single**

Expanded Inside Diameter (Min): **6.4 mm [.25 in]**

Recovered Inside Diameter (Max): **3.2 mm [.126 in]**

Shrink Ratio: **2:1**

[All RNF-3000 Single Wall Stick Heat Shrink \(180\)](#)

Features

Product Type Features

Product Family	RNF-100
Wall Type	Single

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Yellow
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.3 mm[.012 in]
Recovered Wall Thickness (Nominal)	.65 mm[.026 in]
Expanded Inside Diameter (Min)	6.4 mm[.25 in]
Recovered Inside Diameter (Max)	3.2 mm[.126 in]
Heat Shrink Tubing Size Range	3.2 – 6.4 mm[.125 – .25 in]



Usage Conditions

Fluid Resistance	Splash Protection
Shrink Temperature (Min)	95 °C
Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain
Recovery Temperature	121 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Raychem RNF-100



Heat Shrink Tubing(672)




Power Cable Tubing & Accessories(8)

Customers Also Bought



TE Part #ZPF000000000112141
CSR 31000 - RACK POWER SUPPLY - MALE



TE Part #016211-000
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #2411034003
ZHTM: Heat Shrink Tubing, 2:1 Shrink Ratio




TE Part #1743164-2
MQS, CONNECTOR HOUSING



TE Part #160366-2
FF 110 SR. REC 22-20AWG TPBR



TE Part #3160333004
55A1121-20-2/6-9



TE Part #0160793001
99M0111-22-2L



TE Part #1217825-1
FLUORESCENT TUBE SOCKET TERMINAL



TE Part #1SNA167489R2200
BAH21



TE Part #1SNA199400R0600
FEHD1-BE

Documents

[Datasheets & Catalog Pages](#)
[RNF-100 Pages from 9-1773447-9](#)



English

[Application Tooling for Raychem Heat Shrink Product](#)

English

Product Specifications

[Quality Specification](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

German

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)