



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per

homogenous material. Also BFR/CFR/PVC Free

Solder Process CapabilityNot reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 36809 TERMINAL,SOLIS R 6 5/8	 TE Part # 323171 TERMINAL,SOLIS R HR 6 5/16	 TE Part # 36808 TERMINAL,SOLIS R 6 1/2	 TE Part # 320344 TERMINAL,SOLIS R 6 1/2
 TE Part # 130552 SOLIS 6 R M5	 TE Part # 52197 TERMINAL,SOLIS R 6 10	 TE Part # 33467 TERMINAL,SOLIS R 6 3/8	 TE Part # 34322 SPLICE,SOLIS BUTT 6
 TE Part # 33465 TERMINAL,SOLIS R 6 1/4	 TE Part # 33466 TERMINAL,SOLIS R 6 5/16	 TE Part # 321598 TERMINAL,SOLIS R 6 1/4	 TE Part # 34319 SPLICE,SOLIS PARA 6



 TE Part # 321298 TERMINAL,SOLIS R 6 10	 TE Part # 323169 STRATO-THERM, R, HR, 6, #10, NIPL	 TE Part # 1958285-1 SOLISTRAND 6 S-T HR RING 1/4	 TE Part # 2-321598-4 TERMINAL 6 SOLIS RING 1/4
 TE Part # 320745 TERMINAL,SOLIS R 6 7/16	 TE Part # 36810 TERMINAL,SOLIS R 6 3/4	 TE Part # 2-324309-2 SPLICE,SOLIS BUTT 6	 TE Part # 8-52197-2 TERMINAL,SOLIS R 6 10

Customers Also Bought

 TE Part #2-320564-2 PIDG RING TONGUE TERMINALS	 TE Part #322264 TERMINAL,SOLIS R 400MCM 1/2	 TE Part #205558-3 AMPLIMITE,ASY,PLUG,STD,109,2,KIT	 TE Part #45436 HYP8/10 SOLIS 1/0AWG DIE SET
 TE Part #45433 HYP8/10 SOLIS 2AWG DIE SET	 TE Part #3825813001 44A1121-14-0/9-9	 TE Part #183968-000 22759/33-30-1	 TE Part #314270-3 PNEU HD 22-16 PIDG IS9586
 TE Part #ZPF000000000099204 FMJ 11E 12-08 K	 TE Part #312007-000 55A4141-22-MST4-9CS2275		

Documents



Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English