



Application Tooling > Portable Crimp Tools



Die Sets Type: **Removable/Interchangeable**  
Specification Type: **TE Product Specification (114-)**  
TE Certification: **Cannot be Certified**  
Power Technology Type: **Manual**  
Tooling Type: **IDC Tooling**

Features

Other

Crimp Form-Wire Barrel Type	Insulation Displacement
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	IDC Tooling

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 3-330854-0  
MAXI.T.P. CLIP

Customers Also Bought

<div></div> <div><p>TE Part #2-330854-5 MAXI T.P. CLIP</p></div>	<div></div> <div><p>TE Part #1703013-2 ROUND CONNECTOR SYSTEM, PIN AND SOCKET</p></div>	<div></div> <div><p>TE Part #9-160326-2 312 PIDG FASTON REC</p></div>	<div></div> <div><p>TE Part #1241969-8 FASTIN FASTON HOUSING 8P</p></div>
<div></div> <div><p>TE Part #142839-4 TUBING SPIRAP 500029-4</p></div>	<div></div> <div><p>TE Part #165416 P.G.RING DIN</p></div>	<div></div> <div><p>TE Part #2-1415045-1 PT571220</p></div>	<div></div> <div><p>TE Part #2317070-1 SLIDE,HDSCS,PIN HSG ASSY</p></div>



Documents

Datasheets & Catalog Pages

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

TERMI-POINT Tool 69702

English