

CGPT-2.4/1.2-4-SP ✓ ACTIVE

Raychem | Raychem CGPT


TE Internal #: 5068164005

Raychem CGPT, Heat Shrink Tubing, Yellow, Single Wall Type, 2.4 Expanded Inside Diameter (Min) .094 Expanded Inside Diameter (Min)

[View on TE.com >](#)



Heat Shrink Tubing > Single Wall CGPT Spool Heat Shrink Tubin



Primary Product Color: **Yellow**

Wall Type: **Single**

Expanded Inside Diameter (Min): **2.4 mm [.094 in]**

Recovered Inside Diameter (Max): **1.2 mm [.047 in]**

Shrink Ratio: **2:1**

[All Single Wall CGPT Spool Heat Shrink Tubin \(186\)](#)

Features

Product Type Features

| | |
|----------------|--------|
| Product Family | CGPT |
| Wall Type | Single |

Electrical Characteristics

| | |
|---------------|-------|
| Voltage (Max) | .6 kV |
|---------------|-------|

Body Features

| | |
|--------------------------|--|
| Fluid Type | Gasoline, Hydraulic Fluid, Lubricating Oil |
| Primary Product Color | Yellow |
| Shrink Ratio | 2:1 |
| Primary Product Material | Irradiated Modified Polyolefin |
| Flexibility | Flexible |

Dimensions

| | |
|--------------------------------------|------------------------------|
| Recovered Wall Thickness (Tolerance) | .12 mm[.005 in] |
| Recovered Wall Thickness (Nominal) | .5 mm[.02 in] |
| Expanded Inside Diameter (Min) | 2.4 mm[.094 in] |
| Recovered Inside Diameter (Max) | 1.2 mm[.047 in] |
| Heat Shrink Tubing Size Range | 1.2 – 2.4 mm[.047 – .094 in] |



Usage Conditions

| | |
|---------------------------------|-----------------------------------|
| Fluid Resistance | Splash Protection |
| Shrink Temperature (Min) | 80 °C |
| Heat Shrink Tubing Flammability | Flame-Retardant |
| Operating Temperature Range | -40 – 135 °C |
| Heat Shrink Tubing Resistance | Fluids, Mechanical Damage, Strain |
| Recovery Temperature | 120 °C |

Product Availability

| | |
|-------------------|------------|
| Applicable Region | Asia, EMEA |
|-------------------|------------|

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Box |
|------------------|-----|

Other

| | |
|-----------------------------------|----------------|
| Meets Low Outgassing Requirements | No |
| Product Source | Czech Republic |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Raychem CGPT



Heat Shrink Tubing(316)



Power Cable Tubing & Accessories(93)

Customers Also Bought



TE Part #0462-209-16141
DEUTSCH SOLID CONTACTS



TE Part #206070-8
CPC CABLE CLAMPS



TE Part #055124-000
ST18-2-55-20-90



TE Part #W6P
DEUTSCH DT WEDGELOCKS



TE Part #114017-ZZ
DEUTSCH SEALING PLUGS



TE Part #1-480698-0
02P UMNL PLUG HSG NATL



TE Part #1633918-7
ANVIL, COMBINATION

Documents

Product Drawings

[CGPT-2.4/1.2-4-SP](#)

English

Datasheets & Catalog Pages

[Application Tooling for Raychem Heat Shrink Product](#)

English

[CGPT Pages from 9-1773447-9](#)

English

Product Specifications

[Quality Specification](#)



English